

by Wiegmann Catalog ID: WA907220FSD

N12 Double Door Freestanding 90X72X20 Carbon Steel - Gray

Designed to protect electrical, and electronic controls, components, and instruments in typical industrial environments. Enclosure protects enclosure equipment from dust, dirt, oil, and dripping water. These enclosures are used in machine tool applications for housing motor starters, drivers, contactors, PLC's, as well as a wide variety of other electrical and electronic equipment. The addition of 19-inch rack mounting accessories make these enclosures ideal for providing rugged protection for sensitive rack mounted components in harsh industrial environments. The enclosures are found extensively in found in automotive, pulp and paper, wood products, textile, and similar industries. Style includes two door single access (overlapping doors on front).

Product Details

General

Application	Designed to protect electrical and electronic controls, components, and instruments in typical industrial environments. Enclosures protect enclosure equipment from dust, dirt, oil, and dripping water. These enclosures are used in machine tool applications
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Door
Finish Type	Textured
Latches Type	3 Point Keylocking-Padlocking Combo
Listings	UL, CSA
Material	Carbon Steel
Mounting Type	Freestanding
Number of Doors (Fixed)	2
Туре	Enclosure
UPC	786725450251

Dimensions

Actual Depth	20.12 in
Actual Height	90.120 in
Actual Width	72.12 in

Depth	20 in	
Height	90 in	
Weight	883 lb	
Width	72 in	
Certifications and Compliance		
Certified Listed	• UL • CSA	
Nema Rating	NEMA 12	
UL Listed	Yes	