

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male, Plug, 30A 125/250V, 3-Pole 4-Wire Grounding, Terminal Screws, Watertight

By Hubbell Wiring Device-Kellems
Catalog # [HBL430P9W](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male, Plug, 30A 125/250V, 3-Pole 4-Wire Grounding, Terminal Screws, Orange, Watertight

Application

- High Ampacity Connections

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 3,000V AC Min
- Electrical - Max. Working Voltage - 600V AC RMS
- Environmental - Flammability - HB or Better per UL 94 or CSA C22.2 No. 0.17
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Watertight per IEC 60309-1
- Environmental - Operating Temperature - Maximum Continuous 75°C
- Minimum - 40°C w/o impact
- Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 / UL1682
- Mechanical - Product Identification - Identification and ratings are a permanent part of the device housing.
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

General

Catalog Number	HBL430P9W
Color	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Male Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Series	HBL Heavy Duty
Specifications	<ul style="list-style-type: none">• Contact Carrier - High-Impact Thermoset• Housing - Zytel® ST801 Nylon



Style	Standard Service
Type	Watertight Plug
UPC	783585404608

Dimensions

Display Size	Standard Sized
--------------	----------------

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Three Phase
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250 VAC

Conductor Related

Cord Type	All Portable
Number Of Wires	4-Wire
Wire Size	#12 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Standard C22.2 No. 182.1• UL Classified to IEC60309-1• UL Listed, File E146032
Nema Rating	Non-NEMA

Logistics

Carton Quantity	10
Pallet Quantity	320

Product Assets

[Catalog Page - WDK G-6 Catalog Page](#)
[Catalog Page - WDK G-24 Catalog Page](#)
[Catalog Page - WDK G-26 Catalog Page](#)
[Catalog Page - WDK G-10 Catalog Page](#)
[Catalog Page - WDK G-22 Catalog Page](#)
[Catalog Page - WDK G-27 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - HBL430P9W AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1303_INSTALLINST](#)

[Literature - Advantage™ Series Switch-Rated IEC Pin & Sleeve Devices](#)
[Literature - IEC Pin & Sleeve Devices](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - Dual-Certified IEC Pin & Sleeve Devices](#)
[Literature - IEC Pin & Sleeve Devices](#)
[Sales Drawings - WDK_HBL430P_DRAWING_PDF](#)
[Specifications - Wiring HBL430P9W Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK-HBL430P9W-SPEC-EN | REV 4/2025