



WC1224B

by Wiegmann
Catalog ID: WC1224B

N12 Single Door Console Body 36X24X20 Carbon Steel - Gray

WC12 SERIES - 14 GAUGE CARBON STEEL NEMA 12 OPERATOR INTERFACE CONSOLE -SIZE 36.13 IN X 24.13 IN X 20.13 IN.

- Fabricated from carbon steel
- Seams are continuously welded and ground smooth
- Removable back panel is provided with the console
- The large sloping control panel is hinged along the bottom edge

Bodies and doors fabricated from 14 gauge steel. Seams are continuously welded and ground smooth. 3-point keylocking handle is provided on front, main door. Main hinged doors are flush. Large sloping control panels are hinged along the bottom edge. Control panels have captive screws which thread into sealed wells. Grounding provisions included. Door stops provided to hold control panel open. Print pocket is provided. Closed cell neoprene gasket is provided. Removable back panel included with console. Studs are welded to inside of console for mounting back panel.

Product Details

General

Application	Designed to hold electrical and electronic controls and instruments. Pushbuttons, pilot lights, meters, switches, etc., can be mounted on sloping control surfaces. Interior components can be mounted on standard back panel and terminal straps. Heavy duty c
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Door
Finish Type	Polyester Powder
Latches Type	3-Point Keylocking Handle
Listings	UL, CSA
Material	Carbon Steel

Number of Doors (Fixed)	1
Series	WC12
Type	Console Body
UPC	786725443338

Dimensions

Actual Depth	20.13 in
Actual Height	36.130 in
Actual Width	24.13 in
Depth	20 in
Height	36 in
Weight	148 lb
Width	24 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	NEMA 12
UL Listed	Yes