

EdgeConnect™ Series, Straight Blade Devices, Connector, Industrial/Commercial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Black and White

By Hubbell Wiring Device-Kellems
Catalog # [HBL5269CST](#)

EdgeConnect™, Straight Blade Devices, Connector,
Industrial/Commercial Grade, 2-Pole 3-Wire Grounding, 15A 125V,
5-15R, Black and White



Features

- Spring termination for a faster and more secure terminal connection
- Ribbed housing is impact and chemical resistant
- Superior cord grip design protects terminations from excess strain
- Accepts #14 - #10AWG, solid or stranded

Application

Extra Heavy Duty Industrial/Commercial Grade

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - UL 94 V-2, Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact), Mechanical - Product Identification - Ratings are a permanent part of the device, Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only, Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Specifications

| | |
|--------------------------|--|
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| EU RoHS Indicator | Contact Manufacturer |
| Nema Rating | 5-15P |
| Industry Standard(s) | <ul style="list-style-type: none">• CSA Certified to C22.2 No. 42 File 280• Fed. Spec. W-C596G• NEMA® WD-6 Compliant |

Conductor

| | |
|----------------------|--------------------|
| Number Of Conductors | 3-Wire Grounding |
| Number Of Wires | 3-Wire |
| Wire Size | #14 AWG to #10 AWG |
| Number Of Poles | 2-Pole |
| Conductor Range | #14 AWG to #10 AWG |

Configuration

Cord Type

All Listed Portables

Current

| | |
|---------------------------|---------------------------|
| Dielectric Strength | Withstands 2,000V minimum |
| Voltage Rating | 125 V |
| Connectivity | Spring Termination |
| Phase | Single Phase |
| Current / Amperage Rating | 15 A |

Dimensions

| | |
|--------------|-----------------------------|
| Display Size | Standard Sized Product |
| Weight | 0.2 lb. |
| Size | 3.28 in x 1.41 in x 1.09 in |

General

| | |
|------------------------------|---|
| Color | Black and White |
| Style | Standard |
| Cord Range | 0.230"-0.720"(5.8-18.3) |
| Series | EdgeConnect™ Series |
| Specifications | Body - Nylon, Retainer - Polycarbonate, Cover - Nylon, Cord Clamp - Nylon, Contact Blades - Copper Alloy, Spring - Stainless Steel, Plunger - Nylon, Drive/Assembly/Cord Clamp Screws - Steel |
| UPC | 783585965321 |
| Type | Connectors |
| Material - Mounting Hardware | Cord Mounted |
| Insulation | Insulated Body |
| Item Type | Insulgrip® Connector |
| Material | Nylon |

Logistics

| | |
|-----------------|------|
| Pallet Quantity | 5000 |
| Carton Quantity | 10 |

Operational

| | |
|--------------------|--|
| Temperature Rating | <ul style="list-style-type: none">• Maximum continuous 75°C• minimum -40°C (w/o impact) |
|--------------------|--|

Operating Temperature

Maximum continuous 75°C and
minimum -40°C without Impact
0.5

Horsepower - Maximum

Product Assets

[Catalog \[English\]](#)

[Catalog Page \[English\]](#)

[Catalog Page \[English\]](#)

[Installation Manual \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved
WDK-HBL5269CST-SPEC-EN | REV 5/2026