



## WC12B

by Wiegmann  
Catalog ID: WC12B

N12 Console Body 36X36X20 Carbon Steel - Gray

WC12 SERIES - 14 GAUGE CARBON STEEL NEMA 12 OPERATOR INTERFACE CONSOLE -SIZE 36.13 IN X 36.13 IN X 20.13 IN.

- Fabricated from carbon steel
- Seams are continuously welded and ground smooth
- Removable back panel is provided with the console.
- The large sloping control panel is hinged along the bottom edge.

Bodies and doors fabricated from 14 gauge steel. Seams are continuously welded and ground smooth. 3-point keylocking handle is provided on front, main door. Main hinged doors are flush. Large sloping control panels are hinged along the bottom edge. Control panels have captive screws which thread into sealed wells. Grounding provisions included. Door stops provided to hold control panel open. Print pocket is provided. Closed cell neoprene gasket is provided. Removable back panel included with console. Studs are welded to inside of console for mounting back panel.

## Product Details

### General

Application	Designed to hold electrical and electronic controls and instruments. Pushbuttons, pilot lights, meters, switches, etc., can be mounted on sloping control surfaces. Interior components can be mounted on standard back panel and terminal straps. Heavy duty c
Color	Gray
Construction	Continuously Welded Seams
Finish Type	Polyester Powder
Latches Type	3-Point Keylocking Handle
Listings	UL, CSA
Material	Carbon Steel
Series	WC12
Type	Console Body
UPC	786725443208

### Dimensions

Actual Depth	20.13 in
Actual Height	36.130 in

Actual Width	36.13 in
Depth	20 in
Height	36 in
Weight	184 lb
Width	36 in

#### Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul>
Nema Rating	NEMA 12
UL Listed	Yes