


WC1448BD

by Wiegmann
 Catalog ID: WC1448BD

Prop65_Cancer&Reproductive

N12 Double Door Console Body 50X48X23 Carbon Steel - Gray

Designed to hold electrical and electronic controls and instruments. Pushbuttons, pilot lights, meters, switches etc., can be mounted on the instrument panel. Interior components are motorized on stationary sub panels, swing-out sub panels or relay rack angles (panels are optional). Heavy duty construction provides protection from dirt, dust, oil and water. Numerous accessories and variable combinations make these consoles most versatile.



* Representative image

Product Details

General

Application	Designed to hold electrical and electronic controls and instruments. Pushbuttons, pilot lights, meters, switches, etc., can be mounted on the instrument panel. Interior components are motorized on stationary sub panels, swing-out sub panels, or relay rack
Color	Ansi-61 Gray Textured
Construction	Continuously Welded Seams
Cover Type	Door
Finish Type	Polyester Powder
Latches Type	3-Point Keylocking Handle
Listings	UL, CSA
Material	Steel, Carbon
Number of Doors (Fixed)	2
Series	WC14
Type	Console Body
UPC	786725444304

Dimensions

Actual Depth	23.13 in
Actual Height	50.130 in
Actual Width	48.13 in
Depth	23 in

Height	50 in
Weight	290 lb
Width	48 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	12
UL Listed	Yes

Logistics

Carton Quantity	1
-----------------	---