

# **Surge Protective Devices, SPIKESHIELD TVSS Duplex** Receptacle with Light and Alarm, 20A 125V, 5-20R, Gray

By Hubbell Wiring Device-Kellems Catalog # HBL5362GYSA

Surge Protective Devices, SPIKESHIELD TVSS Duplex Receptacle with Light and Alarm, 20A 125V, 5-20R, Gray



Decorator Duplex with Light and Alarm

### General

Color Gray

**Environmental Conditions** 

Indicator(s) Type LED and Audible Alarm

Item Type Surge Protection Receptacles

Material Composite

Material - Mounting Hardware

**OEM Brand Name** 

Operating Temperature

Outlet Performance

Indoor Dry Unless Protected

By Additional Means

Mounting Screws

Hubbell Wiring Device-

32 Deg F to 140 Deg F (O Deg

C to 60 Deg C)

Straight Blade

• Electrical - Protection Modes - Normal and Common Modes

Electrical - Response Time - Approximately 5 ns

• Electrical - Transient Suppression - Peak Energy (10 X 100  $\mu$ s), Peak Current  $(8 \times 20 \mu s)$ 

Electrical - Voltage - 120V AC + 10% - 15%

• Environmental -Flammability - UL 94V-2

Environmental - Operating Temperature - 32°F to 140°F (0°C to 60°C)

Response Time

Series Specification Grade

Туре Duplex

UPC 783585060255

**Dimensions** 

Display Size Standard



## **Electrical Ratings**

20 A Amperage Rating

Terminal Screws Connectivity

Current / Amperage Rating 20 A Current Rating 20 A Frequency Rating 60 Hz Phase Single Phase

Voltage Rating 125 V Voltage Rating Description 125 V

## **Certifications and Compliance**

Industry Standard(s) · CSA Certified to

Specification C22.2 No. 42

• Listed to UL Standards 498

• UL Listed File E2186

Nema Rating 5-20R

Logistics

Carton Quantity 10

### **Product Assets**

Catalog Page - Wiring N-13 Catalog page Catalog Page - Wiring J-4 Catalog page

Catalogs - Wiring Full Catalog

Engineering Drawing - HBL5362GYSA AutoCAD Drawing Installation Manuals - WIRING\_PD1152\_INSTALLINST Literature - SpikeShield® Power Quality Surge Protective

Sales Drawings - WDK HBL5362 DRAWING PDF Warranty - Industrial & Commercial Products

