



# Straight Blade Devices, Receptacles, Duplex, Heavy Duty Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Light Almond

By Hubbell Wiring Device-Kellems  
Catalog # [5662LA](#)



Straight Blade Devices, Receptacles, Duplex, Heavy Duty  
Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Light  
Almond

## Features

- Back and side wired
- Fed- Spec UL listed
- Smooth nylon face, Brass triple-wipe contacts

## Application

Hubbell-Pro Heavy Duty

## General

|                              |   |
|------------------------------|---|
| Color                        | Light Almond  |
| Horsepower - Maximum         | 1.5   |
| Material - Mounting Hardware | Screw Mounting  |
| Number Of Poles              | 2-Pole  |
| OEM Brand Name               | Hubbell Wiring Device-Kellems   |
| Operating Temperature        | Maximum continuous 75°C and minimum -40°C without Impact  |
| Performance                  | <ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Environmental - Flammability - UL 94 V-2</li> <li>• Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)</li> <li>• Mechanical - Product Identification - Ratings are a permanent part of the device</li> <li>• Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only</li> <li>• Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA</li> </ul> |

## Electrical Ratings

|                            |                           |
|----------------------------|---------------------------|
| Amperage Rating            | 15 A                      |
| Connectivity               | Back and Side Wired       |
| Current / Amperage Rating  | 15 A                      |
| Current Rating             | 15 A                      |
| Dielectric Strength        | Withstands 2,000V minimum |
| Voltage Rating Description | 250 V                     |
| Wattage                    | 3750 W                    |

## Conductor Related

|                 |                    |
|-----------------|--------------------|
| Number Of Wires | 3-Wire             |
| Wire Size       | #14 AWG to #10 AWG |

## Certifications and Compliance

|                      |  |
|----------------------|--|
| Industry Standard(s) | <ul style="list-style-type: none"> <li>• Certified to CSA 22.2, No. 42</li> <li>• Fed. Spec. W-C-596</li> <li>• NEMA® WD-6 Compliant</li> <li>• UL Listed to UL498 File No. E2186</li> </ul> |
|----------------------|--|

|             |       |
|-------------|-------|
| Nema Rating | 6-15R |
|-------------|-------|

## Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

## Product Assets

[Catalog Page - Wiring A-23 Catalog page](#)  
[Catalogs - Wiring Full Catalog](#)  
[Engineering Drawing - 5662LA AutoCAD Drawing](#)  
[Literature - Hubbell-PRO 15A & 20A 250V Duplex Receptacles](#)  
[Warranty - Industrial & Commercial Products](#)

## Related Products

[IG5462 - Straight Blade Devices, Receptacles, Duplex, Specification Grade, 2-Pole 3-Wire Grounding, 20A 250V, 6-20R, Orange, Single Pack](#)

[5662LA - Straight Blade Devices, Receptacles, Duplex, Heavy Duty Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Light Almond](#)

[HBL5666CA - Straight Blade Devices, Male Plug, Insulgrip Heavy Duty, Industrial/Commercial Grade, Angled, 2-Pole 3-Wire Grounding, 15A 250V, 6-15P and White](#)

[HBL 5666C - Straight Blade Devices, Male Plug, Insulgrip Heavy](#)

Series Hubbell-PRO  
Style Smooth Face  
Type Standard Duplex  
UPC 783585555829

IG5662 - Straight Blade Devices, Male Plug, Insignia Heavy Duty, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 15A 250V, 6-15P and White  
IG5662 - Straight Blade Devices, Receptacles, Duplex, Specification Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Orange, Single Pack

**Dimensions**

Weight 0.2 lb



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-5662LA-SPEC-EN | REV 5/2023