

HUBBELL
Wiring Device-Kellems

**Straight Blade Devices, Tamper
Resistant Duplex Receptacle,
Hubbell-Pro, Hospital Grade, LED
Indicator, 2-Pole 3-Wire Grounding,
15A 125V, 5-15R, Gray**

By Hubbell Wiring Device-Kellems
Catalog # [8200GYLTRA](#)

Straight Blade Devices, Tamper Resistant Duplex Receptacle,
Hubbell-Pro, Hospital Grade, LED Indicator, 2-Pole 3-Wire
Grounding, 15A 125V, 5-15R, Gray



Features

- Tamper-resistant shutter complies with national electrical code requirements
- Green LED Power Indicators to identify emergency circuits
- Triple wipe contacts
- High impact resistant face with circuit I.D. marking area
- Steel mounting strap

General

Application	Hubbell-Pro Heavy Duty Hospital Grade
Catalog Number	8200GYLTRA
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	0.5
Indicator(s) Type	Green LED
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current Electrical - Dielectric Voltage - Withstands 2,000V minimum Environmental - Flammability - UL 94V-2 Environmental - Operating Temperature - Maximum continuous 75°C, minimum -40°C (w/o impact) Mechanical - Product Identification - Ratings are a permanent part of the device Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA
Series	Hubbell-Pro
Style	Smooth Face
Type	Receptacle
UPC	783585542102

Dimensions

Dimensions	3.28 in x 1.57 in x 1.15 in
Height	1.15 in
Length	3.28 in
Weight	0.2 lb
Width	1.57 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	Certified to CSA, C22.2, No. 42 File 285 Fed. Spec. W-C-596 NEMA® WD-6 Compliant UL Listed to UL498 File No. E2186
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK L-8 Catalog Page](#)
[Catalog Page - WDK A-27 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Literature - Duct Products Guide](#)
[Literature - Tamper-Resistant Receptacles for Healthcare](#)
[Literature - Hubbell-PRO Hospital Grade TR Receptacles](#)
[Literature - Hubbell-Pro Hospital Grade Receptacles](#)
[Literature - Healthcare Application Guide](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Tamper-Resistant Receptacles](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK-8200GYLTRA-SPEC-EN | REV 6/2024