

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 60A 3-Phase Wye 120/208V AC, 4-Pole 5-Wire Grounding, Watertight

By Hubbell Wiring Device-Kellems
Catalog # [HBL560R9W](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 60A 3-Phase Wye 120/208V AC, 4-Pole 5-Wire Grounding, Terminal Screws, Blue, Watertight

Application

- High Ampacity Watertight Connections

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstand 3000V AC
- Electrical - Max. Working Voltage - 600V RMS
- Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Watertight per IEC 60309-1
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum - 40°C w/o impact
- Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 / UL1682
- Mechanical - Product Identification - Ratings are a permanent part of the device housing
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

General

Catalog Number	HBL560R9W
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Single Flanged
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Series	HBL Heavy Duty
Specifications	<ul style="list-style-type: none">• Cover - Reinforced Thermoplastic Polyester• Cover Screw - Nickel-plated brass• Gaskets - Solid Neoprene



Style	Standard Service
Type	Watertight Receptacle
UPC	783585405735

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Phase	Three Phase
Voltage Rating	3 Phase Y 120/208 VAC
Voltage Rating Description	3-Phase 120/208 VAC
Wattage	12480

Conductor Related

Wire Size	#8 AWG to #2 AWG
-----------	------------------

Certifications And Compliance

Buy America(n) Qualified	BABA Compliant (All status valid till December 2024)
Industry Standard(s)	Listed To Standard UL1682
Nema Rating	Non-NEMA

Logistics

Carton Quantity	10
Pallet Quantity	300

Product Assets

[Catalog Page - WDK G-11 Catalog Page](#)
[Catalog Page - WDK G-31 Catalog Page](#)

Catalog Page - WDK H-13 Catalog Page
Catalogs - WDK Catalog Full 2024
Engineering Drawing - HBL560R9W AutoCAD Drawing
Installation Manuals - WIRING_PD1304_INSTALLINST
Literature - IEC Pin & Sleeve Devices
Literature - PULP & PAPER SOLUTIONS
Literature - Pulp & Paper Solutions

Literature - Wiring Device Solutions for Strategic Manufacturing
Facilities
Literature - Entertainment Product Solution Guide
Literature - Dual-Certified IEC Pin & Sleeve Devices
Literature - Emergency Preparedness for Healthcare
Sales Drawings - WDK_HBL560R_DRAWING_PDF
Specifications - Wiring HBL560R9W Specification Sheet
Warranty - Industrial & Commercial Products



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK-HBL560R9W-SPEC-EN | REV 4/2025