



# Occupancy/Vacancy Sensors, Wall Switch, Adaptive Ultrasonic, 2 Circuit, 120/277V AC, Ivory

By Hubbell Wiring Device-Kellems  
Catalog # [AU2000I22](#)

Occupancy/Vacancy Sensors, Wall Switch, Adaptive Ultrasonic, 2 Circuit, 120/277V AC, Ivory

## Features

- Built in photocell with manual super saver mode for daylight harvesting
- No neutral required
- Auto or manual “ON” operating modes. Available in either single relay or dual relay versions
- Designed for use on 120 or 277V AC circuits. No neutral needed for fast retrofits

## General

Color	Ivory
Series	Ultrasonic
Type	Manual/Auto
UPC	783585428772

## Electrical Ratings

Voltage Rating	120/277 VAC
Voltage Rating Description	120/277V AC



## Logistics

Carton Quantity 50

## Product Assets

[Installation Manuals - WIRING\\_PD2768\\_INSTALLINST](#)  
[Warranty - HMOSS Occupancy Motion Sensors](#)

## Related Products

[AD2000BK22 - Occupancy/Vacancy Sensors, Wall Switch, Adaptive Dual Technology, 2 Circuit, 120/277V AC, Black](#)  
[AD2000I22N - Occupancy/Vacancy Sensors, Wall Switch, Adaptive Dual Technology, 2 Circuit, 120/277V AC, No Buttons, Ivory](#)  
[AD2240I2 - Occupancy/Vacancy Sensors, Wall Switch, Adaptive Dual Technology, 2 Circuit, 24V DC, Ivory](#)  
[AD2000LA22 - Occupancy/Vacancy Sensors, Wall Switch, Adaptive Dual Technology, 2 Circuit, 120/277V AC, Light Almond](#)  
[AD2001I22 - Vacancy Sensors, Wall Switch, AdaptiveDual Technology, 2 Circuit, 120/277V AC, Ivory](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-AU2000I22-SPEC-EN | REV 5/2023