



FSP Adapter Panel, 12-Fiber, ST Duplex, 8-Port, Loaded with 8 Adapters, Phosphor Bronze, Blue

By Hubbell Wiring Device-Kellems
Catalog # [FSPSTD6](#)

FSP Adapter Panel, 12-Fiber, ST Duplex, 8-Port, Loaded with 8 Adapters, Phosphor Bronze, Blue



Features

- Wide Range of Adapter Types
- Quick and Easy Snap-in Design
- Premium Quality and High Performance

Application

Interconnect

General

Color	<ul style="list-style-type: none">• Blue• Bleu
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	ST Duplex
Material	Phosphor Bronze
Material - Mounting Hardware	Snap-In
Number Of Ports	12
Performance	<ul style="list-style-type: none">• Electrical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)• Environmental - Operating temperature - 0 °C to +75 °C
Repeatability	0.2 dB
Service Life	500 matings
Single/Multimode	MM
Temperature Rating	-40C to +85C
UPC	662620289236

Dimensions

Display Size 5.1" X 1.1"

Electrical Ratings

Connectivity Receptacle
Insertion Loss 0.30 dB
Return Loss 26

Conductor Related

Fiber Size 125 Micron
Fiber Type Multimode

Certifications and Compliance

Industry Standard(s)

- TIA-568-C.3
- TIA-604-FOCIS

Logistics

Carton Quantity 4

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK-FSPSTD6-SPEC-EN | REV 1/2024