

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male, Plug, 125A 220-240V, 2-Pole 3-Wire Grounding, Terminal Screws, Watertight

By Hubbell Wiring Device-Kellems
Catalog # [HBL3125P6W](#)

Heavy Duty IEC Pin and Sleeve Industrial Grade Male Plug 125A 220-240V, 2-Pole 3-Wire Grounding, Terminal Screws, Watertight

Features

- Solid one-piece pins for reliable electrical contact
- Gasketed sealing ring provides watertight seal
- Heavy duty external cord grips for maximum cord retention

Application

High Ampacity Connections

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstand 3000V AC
- Electrical - Max. Working Voltage - 600V RMS
- Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Watertight per IEC 60309-1
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum - 40°C w/o impact
- Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 / UL1682
- Mechanical - Product Identification - Ratings are a permanent part of the device housing
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

General

Catalog Number	HBL3125P6W
Color	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Male Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole



OEM Brand Name	Hubbell Wiring Device-Kellems
Series	HBL Heavy Duty
Specifications	<ul style="list-style-type: none">• Housing - Zytel® ST801 Nylon• Locking Ring - Reinforced Thermoplastic Polyester• Retainer - High-Impact Thermoset• Sealing Gasket - Solid Neoprene• Terminal Screws - Stainless Steel
Style	Standard Service
Type	Watertight Plug
UPC	783585403168

Dimensions

Display Size	Standard Sized
--------------	----------------

Electrical Ratings

Amperage Rating	125 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	125 A
Current Rating	125 A
Phase	Single Phase
Voltage Rating	220-240 VAC
Voltage Rating Description	220-240 VAC

Conductor Related

Cord Type	All Portable
Number Of Wires	3-Wire
Wire Size	#2 AWG to #1/0 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified File LR280C• UL Classified to IEC Standards 60309-1
----------------------	--

Nema Rating

- UL Listed, File E146033

Non-NEMA

Logistics

Carton Quantity

6

Product Assets

- Catalogs - WDK Catalog Full 2024
- Engineering Drawing - HBL3125P6W AutoCAD Drawing
- Installation Manuals - WIRING_PD1308_INSTALLINST
- Literature - PULP & PAPER SOLUTIONS
- Literature - Pulp & Paper Solutions
- Sales Drawings - WDK_HBL3125P6W_DRAWING_PDF
- Specifications - Wiring HBL3125P6W Specification Sheet
- Warranty - Industrial & Commercial Products

