

HUBBELL
Wiring Device-Kellems

**Industrial Grade, Motor Disconnect, Unfused,
3 Pole, 30A 600V AC, Screw Terminals, IP69k,
NEMA Type 4X, 12 Non-Metallic Sloped Top
Enclosure for Top Feed Applications,
HBLAC2 Aux Contact**

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS30TVFD](#)

Industrial Grade, Motor Disconnect, Unfused, 3 Pole, 30A 600V AC,
Screw Terminals, IP69k, NEMA Type 4X, 12, Non-Metallic Sloped Top
Enclosure for Top Feed Applications, HBLAC2 Aux Contact



Features

- Constructed from corrosion and impact resistant UV stabilized non-metallic material
- Rounded sloped top enclosure has a single flat for top feed applications and supports best practices in hygienic design by shedding dirt and debris
- IP69k and Type 4X,12K water ingress protection and Certified by NSF for hygiene in food processing applications
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements
- Product rating are permanently laser-marked and will not wash off
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements
- Factory installed HBLAC2 auxiliary contact is "Break Before Main Break", 1 set of N/O contacts for VFD applications

Application

Heavy Duty Industrial and/or Washdown

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current & voltage, Electrical - Dielectric Voltage - Withstands 3000V AC minimum, Electrical - Max. Working Voltage - 600V AC RMS, Environmental - Flammability - UL94-5VA and V0 Classification, Environmental - Operating Temperature - Max Continuous 75°C,Min Continuous -40°C w/o impact, Environmental - UV Resistance - All materials are UV stabilized, Mechanical - Impact Resistance - In accordance with UL 746C, Mechanical - Mounting - Non-Metallic - External fully adjustable feet, Mechanical - Product Identification - Identification and ratings are part of external label, Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

Specifications

Industry Standard(s)	cULus Listed
Environmental Conditions	Indoor and Outdoor

Conductor

Wire Size	#14 AWG to #8AWG
-----------	------------------

Configuration



Mounting Method

External fully adjustable feet

Current

Dielectric Strength	Withstands 3000V AC minimum
Current / Amperage Rating	30 A

Dimensions

Weight	2.8 lb.
Height	4.12 in
Hub Size	3/4"

General

Specifications	• Base - Valox® • Enclosure Gasket - Neoprene • Handle - Valox® • Shaft (Unfused) - Valox® • Top - Valox®
----------------	---

Color	Gray
Style	Heavy Duty
Ingress Protection	IP69k, NEMA Type 4X, 12
Product Family	Non-Fused
UPC	783585763491
Type	Disconnect Switches
Material - Mounting Hardware	Stainless Steel Screw Mounting
Enclosure Type	IP69k and UL Type 4X, 12

Logistics

Pallet Quantity	360
Carton Quantity	1

Operational

Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Without Impact Maximum continuous 75°C and minimum -40 °C
Horsepower - Maximum	15

Product Assets

[Catalog Page \[English\]](#)
[Installation Manual \[English\]](#)