

Switches and Lighting Controls,
Industrial Grade, Variable
Frequency Drive, Disconnect
Switches, Unfused Switch

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS3PVFD](#)



Switches and Lighting Controls, Industrial Grade, Variable
Frequency Drive, Disconnect Switches, Unfused Switch, Three
Pole, 30A 600V AC, , LED Illumination, Screw Terminals, Gray,
NEMA

Features

- Six highly visible integral phase identification LEDs for use on 3 Phase Y system
- LEDs provide secondary means of visual confirmation of make/break on all phases
- Cover cannot be removed with switch in the “ON” position
- Verification of opening of load side contacts
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements

Application

LED Indicators / Labelless

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current & voltage
- Electrical - Dielectric Voltage - Withstands 3000V AC minimum
- Electrical - Max. Working Voltage - 600V AC RMS
- Environmental - Flammability - UL94-5VA and V0 Classification
- Environmental - Operating Temperature - Max Continuous 75°C,Min Continuous -40°C w/o impact
- Environmental - UV Resistance - All materials are UV stabilized
- Mechanical - Impact Resistance - In accordance with UL 746C
- Mechanical - Mounting - Non-Metallic - External fully adjustable feet
- Mechanical - Product Identification - Identification and ratings are part of external label
- Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

General

Catalog Number HBLDS3PVFD
EU RoHS Indicator No

Enclosure Type	Type 4X, IP69k
Mounting Method	External fully adjustable feet
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Non-Fused
Size	8.5 in x 6 in x 4.12 in
Style	inSIGHT
Type	Disconnect Switches
UPC	783585714271

Dimensions

Dimensions	8.5 in x 6 in x 4.12 in
Height	4.12 in
Length	8.5 in
Width	6 in

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A

Certifications And Compliance

Certified Listed	UL Listed
Industry Standard(s)	UL Listed

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK F-3 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_HBLDS3VFD_INSTALLINST](#)
[Literature - Education Application Guide](#)
[Literature - Improved Short Circuit Current Ratings \(SCCR\)](#)
[Literature - Circuit-Lock® Motor Disconnects](#)
[Specifications - HBLDS3PVFD](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK-HBLDS3PVFD-SPEC-EN | REV 3/2025