

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Connector Body, 30A 3-Phase Delta 250V AC, Watertight

By Hubbell Wiring Device-Kellems
Catalog # [HBL430C9W](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Connector Body, 30A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Terminal Screws, Blue, Watertight

Features

- Insulated Non-Metallic housing
- Color coded housings by voltage for easy identification
- Corrosion-resistant self-closing gasketed cover

Application

- High Ampacity Connections

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - 3000V AC
- Electrical - Max. Working Voltage - 600V RMS
- Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Watertight per IEC 60309-1
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum - 40°C w/o impact
- Mechanical - Impact Resistance - Per CSA C22.2 No.182.1 /UL1682
- Mechanical - Product Identification - Identification and ratings are a permanent part of the device housing
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

General

Catalog Number	HBL430C9W
Color	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Standard
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Series	HBL Heavy Duty



Specifications

- Cord Clamps - Reinforced Thermoplastic Polyester
- Covers - Reinforced Thermoplastic Polyester
- Gaskets - Solid Neoprene
- Glands - Solid Neoprene
- Housing - Zytel® ST801 Nylon

Style

Standard Service

Temperature Rating

Maximum Continuous: 75° C;
Minimum Continuous: -40° C w/o impact, -25° with impact.
Watertight Connector Body
783585404547

Type

UPC

Dimensions

Display Size

Standard

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250 VAC

Conductor Related

Conductor Range	#12 AWG to #8 AWG
Number Of Wires	4-Wire
Number of Conductors	4-Wire Grounding

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified File LR280C• UL Classified to IEC 60309-1 IEC 60309-2• UL Listed, File E146033
Nema Rating	Non-NEMA

Logistics

Carton Quantity 10
Pallet Quantity 280

Product Assets

Catalog Page - WDK G-10 Catalog Page
Catalogs - WDK Catalog Full 2024
Engineering Drawing - HBL430C9W AutoCAD Drawing
Installation Manuals - WIRING_PD1303_INSTALLINST

Literature - IEC Pin & Sleeve Devices
Literature - PULP & PAPER SOLUTIONS
Literature - Pulp & Paper Solutions
Literature - Dual-Certified IEC Pin & Sleeve Devices
Literature - IEC Pin & Sleeve Devices
Sales Drawings - WDK_HBL430C_DRAWING_PDF
Specifications - Wiring HBL430C9W Specification Sheet
Warranty - Industrial & Commercial Products

