

Hubbell Wiring Device Kellems, IEC  
Pin and Sleeve, Inlet, 32A 380-415V,  
3-Pole 4-Wire Grounding,  
Watertight

By Hubbell Wiring Device-Kellems  
Catalog # [HBL432B3W](#)

Hubbell Wiring Device Kellems, IEC Pin and Sleeve, Inlet, 32A  
380-415V, 3-Pole 4-Wire Grounding, Watertight

Features

- Rugged one-piece housing
- Thermoset polyester contact carrier
- Solid one-piece pins for reliable electrical contact

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - 3000V AC
- Electrical - Max. Working Voltage - 600V RMS
- Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Watertight per IEC 60309-1.
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum - 40°C w/o impact
- Mechanical - Cord Grip Retention - Per CSA C22.2 No.182.1 /UL1682
- Mechanical - Product Identification - Identification and ratings are a permanent part of the device housing
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

General

Catalog Number	HBL432B3W
Color	Red
EU RoHS Indicator	Contact Manufacturer
Number Of Poles	3-Pole
Series	Advantage Switch-Rated
Specifications	<ul style="list-style-type: none"><li>• Contact Carrier - High-Impact Thermoset</li><li>• Gaskets - Solid Neoprene</li><li>• Housing - Zytel® 101 Nylon</li></ul>



Style	• Locking Ring - Reinforced Thermoplastic Polyester
Type	• Phase Pins - Brass
UPC	IP69k NEMA 4X Watertight Mating Inlet 783585574561

Electrical Ratings

Amperage Rating	32 A
Current / Amperage Rating	32 A
Voltage Rating Description	380 V 50Hz/440 V 60Hz

Conductor Related

Number Of Wires	4-Wire
-----------------	--------

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Certified File LR280C</li><li>• UL Classified to IEC 60309-1 IEC 60309-2</li><li>• UL Listed, File E146032</li></ul>
----------------------	------------------------------------------------------------------------------------------------------------------------------------------------------------------

Product Assets

- [Catalog Page - WDK G-6 Catalog Page](#)
- [Catalog Page - WDK G-10 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBL432B3W AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD1304\\_INSTALLINST](#)
- [Literature - Advantage™ Series Switch-Rated IEC Pin & Sleeve Devices](#)
- [Literature - IEC Pin & Sleeve Devices](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK\\_HBL432B3W\\_DRAWING\\_PDF](#)
- [Specifications - Wiring HBL432B3W Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Advantage Series Switch-Rated Pin & Sleeve](#)