

HUBBELL
Wiring Device-Kellems

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 60A 3-Phase Delta 250V AC, Watertight, 3/4" NPT Liquidtight Threading

By Hubbell Wiring Device-Kellems
Catalog # [HBL460C9WLT](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 60A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Terminal Screws, Blue, Watertight



*Representative Image

Features

- Insulated Non-Metallic housing
- Color coded housings by voltage for easy identification
- Corrosion-resistant self-closing gasketed cover

General

Application	High Ampacity Connections
Catalog Number	HBL460C9WLT
Color	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Standard
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current Electrical - Dielectric Voltage - Withstand 3000V AC Electrical - Max. Working Voltage - 600V RMS Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17 Environmental - Ingress Protection - IP67 Suitability Environmental - Moisture Resistance - Watertight per IEC 60309-1 Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum - 40°C w/o impact Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 / UL1682 Mechanical - Product Identification - Ratings are a permanent part of the device housing Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions
Series	HBL Heavy Duty
Style	Standard Service
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Watertight Connector Body
UPC	783585550336

Dimensions

Display Size	Standard
--------------	----------

Electrical Ratings

Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating Description	3 Phase 250 VAC

Conductor Related

Conductor Range	#8 AWG to #2 AWG
Number Of Wires	4-Wire
Number of Conductors	4-Wire Grounding

Certifications And Compliance

Industry Standard(s)	CSA Certified File LR280C UL Classified to IEC 60309-1 IEC 60309-2 UL Listed, File E146033
Nema Rating	Non-NEMA

Logistics

Carton Quantity	10
Pallet Quantity	180

Product Assets

[Engineering Drawing - HBL460C9W AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1303_INSTALLINST](#)
[Sales Drawings - WIRING_M-13308_SALESDRAWING](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK-HBL460C9WLT-SPEC-EN | REV 6/2024