

Motorized Cord Reel, 25ft, #10/3
SJO, Wire Leads

By Hubbell Wiring Device-Kellems
Catalog # [HBLM25103](#)

Motorized Cord Reel, 25ft, #10/3 SJO, Wire Leads

Features

- Durable, Corrosion Resistant Cast Aluminum Housing and Base
- UL Type 9
- Multi-Position Guide Arm can be mounted in two different positions
- Ratchet lock automatically maintains desired cord length or can be disengaged in the field for constant tension applications

General

| | |
|----------------|-----------|
| Cable Length | 25 (7.62) |
| Cable Type | 10/3 SJO |
| Catalog Number | HBLM25103 |
| Color | White |
| Series | Motorized |



| | |
|-------|--------------|
| Style | Industrial |
| UPC | 783585974422 |

Electrical Ratings

| | |
|---------------------------|------|
| Current / Amperage Rating | 30 A |
| Voltage Rating | 250 |

Certifications And Compliance

| | |
|----------------------|---------------|
| Industry Standard(s) | UL 355 Listed |
|----------------------|---------------|

Product Assets

[Brochures - INREACH® Motorized Cord Reels](#)
[Literature - inREACH™ Motorized Cord Reels - FAQ](#)
[Specifications - HBLM25103](#)
[Video - inREACH motorized cord reel](#)
[Video - inREACH Motorized Cord Reel](#)