



Surge Protective Devices, SPIKESHIELD Panel Style, 36KA Single Phase

By Hubbell Wiring Device-Kellems
Catalog # [HBLSDSA36](#)



Surge Protective Devices, SPIKESHIELD Panel Style, 36KA
Single Phase

Features

- Excellent for OEM applications
- Installed on the line side or load side of the service entrance

Application

Surface Mount Brick with Leads

General

EU RoHS Indicator	No
Environmental Conditions	Indoor and Outdoor
Indicator(s) Type	Green Status LED per Line
Item Type	Wired-In Surge Arrestors
Material	Steel
Material - Mounting Hardware	Mounting Screws
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	-40 Degrees F to 149 Degrees F (-40 C to 65 C)
Performance	<ul style="list-style-type: none"> • Electrical - Diagnostics - Green Status LED per line • Electrical - Surge Current per Phase - 36kA • Environmental - Operating Temperature - -40°F to 160°F(-40°C to 70°C) • Mechanical - Terminal Accommodation - #14 AWG Wire Leads
Response Time	5
Series	Wired-In Surge Devices
Type	36kA
UPC	783585120874

Dimensions

Display Size 36kA Peak

Electrical Ratings

Connectivity	Leads
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	<ul style="list-style-type: none"> • Single Phase 120 VAC • Single Phase 240 VAC
Voltage Rating Description	120/240 VAC Single Phase

Certifications and Compliance

Industry Standard(s) UL1449-3rd Edition

Product Assets

- [Catalog Page - Wiring N-7 Catalog page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Catalogs - Acme Electric Catalog - Section 9 - Power Conditioning Products](#)
- [Engineering Drawing - HBLSDSA36 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_HBLSDSA36_INSTALLINST](#)
- [Literature - SpikeShield® Power Quality Surge Protective Devices](#)
- [Sales Drawings - WDK_HBLSDSA36_DRAWING_PDF](#)
- [Warranty - SPD Series: 36kA, 40kA & 80kA](#)



A proud member of the Hubbell Family.