



Surge Protective Devices, SPIKESHIELD TVSS Duplex Receptacle with Light, 15A 125V, 5- 15R, White

By Hubbell Wiring Device-Kellems
Catalog # [HBL5260WSA](#)



Surge Protective Devices, SPIKESHIELD TVSS Duplex
Receptacle with Light, 15A 125V, 5-15R, White

Application

Decorator Duplex

General

Color	White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	None
Item Type	Surge Protection Receptacles
Material	Composite
Material - Mounting Hardware	Mounting Screws
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Performance	<ul style="list-style-type: none"> • Electrical - Protection Modes - Normal and Common Modes • Electrical - Response Time - Approximately 5 ns • Electrical - Transient Suppression - Peak Energy (10 X 100 μs), Peak Current (8 X 20 μs) • Electrical - Voltage - 120V AC + 10% - 15% • Environmental - Flammability - UL 94V-2 • Environmental - Operating Temperature - 32°F to 140°F (0°C to 60°C)
Response Time	5
Series	Specification Grade
Type	Duplex
UPC	783585219905

Dimensions

Display Size Standard

Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified to Specification C22.2 No. 42 • Listed to UL Standards 498 • UL Listed File E2186
----------------------	---

Nema Rating 5-15R

Logistics

Carton Quantity 10

Product Assets

- [Catalog Page - Wiring N-13 Catalog page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Engineering Drawing - HBL5260WSA AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1152_INSTALLINST](#)
- [Literature - Residential Product Guide](#)
- [Literature - Residential Catalog](#)
- [Sales Drawings - WDK_HBL5260_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)



