



Wiring Device-Kellems

Signal and Control, Mini Quick, Male Plug, Field Attachable, Angled, 4-Pole, .24"-.32" Cable Range

By Hubbell Wiring Device-Kellems
Catalog # [HPMA04F9](#)



Signal and Control, Mini Quick, Male Plug, Field Attachable, Angled, 4-Pole, .24"-.32" Cable Range

Features

- Superior Contact Design
- Body with High Impact Design
- Precision Wire Funnels Eliminate Stray Strands

Application

Quick Connect/Disconnect Signal and Control

General

EU RoHS Indicator	No
Environmental Conditions	IP67 Ingress Protection
Item Type	Male Angled Plug
Material - Coupling Nut	Aluminum
Material - Insert	PUR/PA
Material - O-Ring	Neoprene
Material - Overmold	PBT
Material - Shell	PBT
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	-40 Deg C to 85 Deg C
Performance	<ul style="list-style-type: none"> • Electrical - Amperage - 3 Pin - 12A • 4,5 Pin - 9A • Electrical - Maximum Wire Size - #16 AWG • Electrical - Voltage Rating - 250V • Environmental - Moisture Resistance - IP66 Suitability • Environmental - Operating Temperature - -40°C to 85°C
Thread Size	Non-Threaded
UPC	783585192208

Electrical Ratings

Amperage Rating	9 A
Current / Amperage Rating	9 A
Current Rating	9 A
Voltage Rating	250V kV

Conductor Related

Cable Size	.24"-.32"
Cable Specification	UL Listed Portable Cord

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07 • UL 2238 and UL50E, File No. E192071
----------------------	---

Logistics

Carton Quantity	30
-----------------	----

Product Assets

- [Literature - WIRING_WLFVM034](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK_HPMA_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

