




Straight Blade Devices, Female Connector Body, Corrosion Resistant, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R

By Hubbell Wiring Device-Kellems
Catalog # [HBL52CM69V](#)



Straight Blade Devices, Female Connector Body, Corrosion Resistant, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding , 15A 125V, 5-15R, Yellow, Single Pack

Application

Marine Grade

General

Color	Yellow
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Valise
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Performance	<ul style="list-style-type: none">Electrical - Dielectric Voltage - Withstands 2,000V minimumElectrical - Max. Working Voltage - 125V or 250V as ratedElectrical - Temperature Rise - Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%Environmental - Flammability - UL 94V-2Environmental - Operating Temperature - Maximum continuous 75°Cminimum -40°C (w/o impact)Mechanical - Product Identification - Molded Rating on Device FaceMechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA (Brass, White, Green)

Dimensions

Display Size	Standard
--------------	----------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	125 VAC

Conductor Related

Conductor Range	#14 AWG to #12 AWG
Number Of Conductors	3-Wire Grounding

Certifications and Compliance

Industry Standard(s)	UL Listed
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Wiring_Catalog_BB37_CatPage](#)
[Catalogs - Wiring Full Catalog](#)
[Installation Manuals - WIRING_PD1558_INSTALLINST](#)
[Literature - Hubbell Marine Full Line Catalog](#)
[Sales Drawings - WDK_HBL52CM69V_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)

Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
UPC	783585808291



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-HBL52CM69V-SPEC-EN | REV 5/2023