

Surge Protective Devices, SPIKESHIELD IG
TVSS Duplex Receptacle with Light and
Alarm, 15A 125V, 5-15R, Blue

By Hubbell Wiring Device-Kellems
Catalog # [IG5262SA](#)

Surge Protective Devices, SPIKESHIELD IG TVSS Duplex
Receptacle with Light and Alarm, 15A 125V, 5-15R, Blue

Features

- Automatic self-grounding staple
- Distinctive surge symbol provides quick identification
- Power-on indicator light verifies that power is available
- Alert alarm sounds when surge protection is no longer functioning

Application

Decorator Duplex with Light and Alarm

Performance

Electrical - Protection Modes - Normal and Common Modes,
Electrical - Response Time - Approximately 5 ns, Electrical -
Transient Suppression - Peak Energy (10 X 100 μ s), Peak Current
(8 X 20 μ s), Electrical - Voltage - 120V AC + 10% - 15%,
Environmental - Flammability - UL 94V-2, Environmental -
Operating Temperature - 32°F to 140°F (0°C to 60°C)

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified to Specification C22.2 No. 42• Listed to UL Standards 498• UL Listed File E2186
Nema Rating	5-15R

Current

Current Rating	15 A
Amperage Rating	15 A
Frequency Rating	60 Hz
Voltage Rating Description	125 V
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Terminal Screws
Voltage Rating	125 V



Dimensions

Display Size	Standard
--------------	----------

General

Series	Specification Grade
OEM Brand Name	Hubbell Wiring Device-Kellems
Outlet	Straight Blade
Style	Isolated Ground
Color	Blue
Item Type	Surge Protection Receptacles
Material - Mounting Hardware	Mounting Screws
Type	Duplex
Material	Composite
Specifications	<ul style="list-style-type: none">• Base Material - Nylon• Contact Design - Tandem Modified Bypass• Face Material - Nylon• Mounting Strap - .050" (1.3) Steel-Zinc Coated• Power Contact - .031" (.8) Brass
UPC	783585060699

Logistics

Carton Quantity	10
-----------------	----

Operational

Response Time	5
Indicator(s) Type	LED and Audible Alarm
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)

Product Assets

- [Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[English\]](#)