



# Hospital Grade Surge Suppression Receptacle, 20A 125V, 5-20R, Gray

By Hubbell Wiring Device-Kellems  
Catalog # IG8362GYSA

Hospital Grade Surge Suppression Receptacle, 20A 125V, 5-20R, Gray



## Features

- High-impact nylon face resists breakage
- Automatic grounding clip attached to bridge
- Power-on indicator light verifies instantly that power is available
- Distinctive surge symbol provides quick visual identification of surge suppression receptacle

## Application

Decorator Duplex with Light and Alarm

## General

Color	Gray
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED and Audible Alarm
Item Type	Surge Protection Receptacles
Material	Composite
Material - Mounting Hardware	Mounting Screws
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Performance	<ul style="list-style-type: none"> <li>• Electrical - Frequency - 60Hz</li> <li>• Electrical - Protection Modes - Normal and Common Modes</li> <li>• Electrical - Response Time - Approximately 5 ns</li> <li>• Electrical - Transient Suppression - Peak Energy (10 X 100 <math>\mu</math>s) Peak Current (8 X 20 <math>\mu</math>s)</li> <li>• Electrical - Voltage - 120V AC + 10% - 15%</li> <li>• Environmental - Flammability - UL 94V-2</li> <li>• Environmental - Operating Temperature - 32°F to 140°F (0°C to 60°C)</li> </ul>
Response Time	5
Series	Hospital Grade
Style	Isolated Ground

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified to Specification C22.2 No. 42</li> <li>• Listed to UL Standards 498 Receptacles</li> <li>• UL Listed File E2186</li> </ul>
Nema Rating	5-20R

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Wiring M16 Catalog page](#)  
[Catalog Page - Wiring N-13 Catalog page](#)  
[Catalogs - Wiring Full Catalog](#)  
[Engineering Drawing - IG8362GYSA AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD1152\\_INSTALLINST](#)  
[Literature - WLBD026\\_Duct Products Brochure\\_WEB](#)  
[Literature - Healthcare Application Guide](#)  
[Literature - SpikeShield® Power Quality Surge Protective Devices](#)  
[Sales Drawings - WDK\\_IG8362\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)

## Related Products

[SS8 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) Duplex Opening, Standard Size, Stainless Steel](#)  
[HBL5360WSA - Surge Protective Devices, Straight Blade Receptacle, Duplex, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, White](#)  
[IG5362GYSA - IG TVSS Duplex Receptacle with Light and Alarm, 20A 125V, 5-20R, Gray](#)  
[HBL420S - Surge Protective Devices, 4-PLEX, Surge Suppression Receptacle, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Blue.](#)  
[IG8262GYSA - Hospital Grade Surge Suppression Receptacle, Isolated Ground, 15A 125V, 5-15R, Gray](#)

Type Duplex  
UPC 783585960470

**Dimensions**

Display Size Standard



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-IG8362GYSA-SPEC-EN | REV 5/2023