

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 60A 3-Phase Wye 277/480V AC, Watertight, 1" NPT Liquidtight Threading

By Hubbell Wiring Device-Kellems
Catalog # [HBL560C7WLT100](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 60A 3-Phase Wye 277/480V AC, 4-Pole 5-Wire Grounding, Terminal Screws, Red, Watertight

Features

- Insulated Non-Metallic housing
- Color coded housings by voltage for easy identification
- Corrosion-resistant self-closing gasketed cover

Application

High Ampacity Connections

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstand 3000V AC
- Electrical - Max. Working Voltage - 600V RMS
- Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Watertight per IEC 60309-1
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum - 40°C w/o impact
- Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 / UL1682
- Mechanical - Product Identification - Ratings are a permanent part of the device housing
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

General

Catalog Number	HBL560C7WLT100
Color	Red
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Standard
Material - Mounting Hardware	Cord Mounted



*Representative Image

Number Of Poles	4-Pole
Series	HBL Heavy Duty
Specifications	<ul style="list-style-type: none">• Cord Clamps - Reinforced Thermoplastic Polyester• Covers - Reinforced Thermoplastic Polyester• Gaskets - Solid Neoprene• Glands - Solid Neoprene• Housing - Zytel® ST801 Nylon
Style	Standard Service
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Watertight Connector Body
UPC	783585714745

Dimensions

Display Size	Standard
--------------	----------

Electrical Ratings

Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating Description	3 Phase Y 277/480 VAC

Conductor Related

Conductor Range	#8 AWG to #2 AWG
Number Of Wires	5-Wire
Number of Conductors	5-Wire Grounding

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified File LR280C• UL Classified to IEC 60309-1 IEC 60309-2• UL Listed, File E146033
----------------------	--

Nema Rating	Non-NEMA	Engineering Drawing - HBL560C7W AutoCAD Drawing
Logistics	10	Installation Manuals - WIRING_PD1303_INSTALLINST
		Sales Drawings - WDK_HBL560C_DRAWING_PDF
Carton Quantity		Specifications - HBL560C7WLT100
Product Assets		Warranty - Industrial & Commercial Products

