



Field Attachable Micro-Quick Control Connectors, Female Straight, 3 Wire, Insulation Displacement

By Hubbell Wiring Device-Kellems
Catalog # [MCMS131DCL](#)



Field Attachable Micro-Quick Control Connectors, Female Straight, 3 Wire, Insulation Displacement

Features

- Strain relief bushing protects terminations
- Wire Guide for virtually toolless termination
- Insulation displacement contacts are made of Copper Alloy

Application

Quick Connect/Disconnect Signal and Control

General

Color	Black
EU RoHS Indicator	Yes
Item Type	Female Straight Plug
OEM Brand Name	Hubbell Wiring Device-Kellems
Performance	<ul style="list-style-type: none">• Electrical - Amperage - 6A• Electrical - Cable Diameters - .22" to .32"• Electrical - Voltage Rating - 50V AC/DC• Electrical - Wire Range - #18 AWG max., #22 AWG min.• Environmental - Ingress Protection - IP66 Suitability• Environmental - Operating Temperature - -20°C to 110°C
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585226750

Dimensions

Diameter Live Part .59"

Conductor Related

Conductor Type Copper
Number Of Conductors 3-Pole

Certifications and Compliance

Industry Standard(s)

- CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07
- UL 2238 and UL50E, File No. E192071

Logistics

Carton Quantity 25

Product Assets

[Installation Manuals - WIRING_PD1939_INSTALLINST](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_MCMS131DCL_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-MCMS131DCL-SPEC-EN | REV 5/2023