

# Straight Blade Devices, Receptacles, Single, Specification Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Brown, Single Pack

By Hubbell Wiring Device-Kellems  
Catalog # [HBL5661](#)



Straight Blade Devices, Receptacles, Single, Specification Grade,  
2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Brown, Single Pack

## Application

- Extra Heavy Duty

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - Top: UL 94V-2, Base: UL 94V-0
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

## General

Catalog Number	HBL5661
Color	Brown
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1.5
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none"><li>• Auto Self-grounding Clip - Stainless steel</li><li>• Base - PBT</li><li>• Face - Nylon</li><li>• Ground Contact - Brass</li><li>• Mounting Screws - Zinc plated steel</li></ul>

Style  
Type  
UPC

- Mounting Strap - .050" (1.3) Brass
  - Power Contacts - .037 in. (.9) Brass
- Finder Groove Face  
Single Receptacle  
783585013992

## Dimensions

Dimensions	1.94 in x 1.63 in x 1.19 in
Display Size	Standard Sized Product
Height	1.19 in
Length	1.94 in
Weight	0.15 lb
Width	1.63 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	3750 W

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

## Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA 22.2, No. 42 File 285</li><li>• Guide RTRT Fed Spec WC596G</li></ul>

- NEMA® WD-6 Compliant
- UL Listed to UL498 File No. E2186

Nema Rating 6-15R  
Standards - RoHS Compliance CM  
Status

### Logistics

Carton Quantity 10  
Pallet Quantity 5500

### Product Assets

[Catalog Page - WDK O-33 Catalog Page](#)

[Catalog Page - WDK A-12 Catalog Page](#)  
[Catalog Page - WDK N-18 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - HBL5661 AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD2504\\_INSTALLINST](#)  
[Installation Manuals - WIRING\\_PD2615\\_INSTALLINST](#)  
[Literature - EdgeConnect™ Technology FAQ](#)  
[Literature - PULP & PAPER SOLUTIONS](#)  
[Literature - Pulp & Paper Solutions](#)  
[Literature - Industrial Solutions](#)  
[Sales Drawings - WDK\\_HBL5661\\_DRAWING\\_PDF](#)  
[Specifications - Wiring HBL5661 Specification Sheet](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand