



Signal and Control, Micro Quick, Male Plug, Field Attachable, Angled, 5-Pole, .24-.32" Cable Range

By Hubbell Wiring Device-Kellems
Catalog # [MIMA15F9](#)



Signal and Control, Micro Quick, Male Plug, Field Attachable, Angled, 5-Pole, .24-.32" Cable Range

Features

- Body with high impact design
- Strain relief protects terminations
- Precision wire funnels eliminate stray strands

Application

Quick Connect/Disconnect Signal and Control

General

EU RoHS Indicator	No
Environmental Conditions	IP67 Ingress Protection
Item Type	Male In-Line Angle Plug
Material - Coupling Nut	Aluminum
Material - Insert	PUR/PA
Material - O-Ring	Neoprene
Material - Overmold	PBT
Material - Shell	PBT
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	-40 Deg C to 85 Deg C
Performance	<ul style="list-style-type: none">• Electrical - Amperage - 4A• Electrical - Maximum Wire Size - #18 AWG• Electrical - Voltage Rating - 250V• Environmental - Moisture Resistance - IP66 Suitability• Environmental - Operating Temperature - -40°C to 90°C
Thread Size	Non-Threaded
UPC	783585192567

Electrical Ratings

Amperage Rating	4 A
Current / Amperage Rating	4 A
Current Rating	4 A
Voltage Rating	250V kV

Conductor Related

Cable Size	.24"-.32"
Cable Specification	UL Listed Portable Cord

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07• UL 2238 and UL50E, File No. E192071
----------------------	--

Logistics

Carton Quantity	30 EA
-----------------	-------

Product Assets

[Literature - WIRING_WLFVM034](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_MIMA15F9_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-MIMA15F9-SPEC-EN | REV 5/2023

