

## **Straight Blade Devices, Receptacles, RTP, Industrial Grade, 3-Pole 4-Wire Grounding, 30A 125/250V, 14-30R, Black, Single Pack.**

By Hubbell Wiring Device-Kellems  
Catalog # [HBL9430A](#)

Designed for plug-in EV charging applications, Hubbell's 14-50R receptacle is a premium and dependable solution to exceed the requirements of electric vehicle owners. This receptacle ensures a safe and efficient charging experience, providing peace of mind to EV users.

### **Features**

- **Tailored for EV Charging:** This receptacle is purpose-built to cater to the specific needs of EV charging. It incorporates features and specifications that are optimized for the safe and efficient charging of electric vehicles.
- **Industrial-Grade Construction:** This EV receptacle boasts a robust and durable construction. It is engineered using high quality materials that can withstand demanding environments, ensuring long-lasting performance and reliability.
- **Secure Connection:** Terminal box shields against loose wires and external damage with a durable enclosure. Features a clamping mechanism for tight, efficient wire termination, reducing power loss or overheating risks.
- **Contact Force & Durability:** Thick wall terminal box offers 50% greater contact force for secure connections, minimizing power interruptions. Designed for heavy use, it withstands frequent insertions and removals, ensuring lasting performance.
- **Fast & Efficient Charging:** Features a 3-pole, 4-wire grounding for secure EV charging, minimizing electrical faults. With a 50A, 125/250V rating, it ensures high-power, faster charging times, promoting safety and efficiency.
- **Effortless Installation:** This EV Charging Receptacle is designed for easy setup, featuring a straightforward wiring mechanism suitable for both professional electricians and DIY enthusiasts, ensuring a hassle-free installation process.



### **Performance**

- **Electrical - Current Interrupting** - Certified for current interrupting at full rated current
- **Electrical - Dielectric Voltage** - Withstands 2,000V minimum
- **Environmental - Flammability** - UL 94 V-0
- **Environmental - IP Suitability** - IP20
- **Environmental - Operating Temperatures** - Maximum continuous 75°C, minimum -40°C (w/o impact)
- **Mechanical - Product Identification** - Ratings are a permanent part of the device
- **Mechanical - Terminal Accommodation** - #12 AWG through #4 AWG copper wire only
- **Mechanical - Terminal Identification** - Terminals identified in accordance with UL 498 and CSA

### **General**

Catalog Number	HBL9430A
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Style	Grounding
Type	Receptacle
UPC	783585015293

## Dimensions

Dimensions	3.28 in x 2.75 in x 2.44 in
Display Size	Standard Sized Product
Height	2.44 in
Length	3.28 in
Weight	0.65 lb
Width	2.75 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	<ul style="list-style-type: none"><li>125/250 V</li><li>125 V V</li></ul>
Voltage Rating Description	125/250 V
Wattage	7500 W

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#12 AWG to #4 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>Certified to CSA</li><li>NEMA® WD-6 Compliant</li><li>UL Listed File E2186</li></ul>
Nema Rating	14-30R

## Logistics

Carton Quantity	5
Pallet Quantity	1800

## Product Assets

[Catalog Page - WDK N-18 Catalog Page](#)  
[Catalog Page - WDK A-47 Catalog Page](#)  
[Catalog Page - WDK A-69 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - HBL9430A AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD1186\\_INSTALLINST](#)  
[Literature - Electric Vehicle Charger Receptacle](#)  
[Literature - Pulp & Paper Solutions](#)  
[Literature - PULP & PAPER SOLUTIONS](#)  
[Sales Drawings - WDK\\_HBL9430A\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)  
[Video - Insulgrip Twist-Lock and Straight Blade Devices](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK-HBL9430A-SPEC-EN | REV 7/2024