

Industrial Grade, Disconnect
Switches, Unfused Switch, Break
before Main Break Auxiliary
Contact, For 30A 60A and 100A,
Pilot Duty.

By Hubbell Wiring Device-Kellems
Catalog # [HBLAC2](#)

Switches and Lighting Controls, Industrial Grade, Disconnect
Switches, Unfused Switch, Break before Main Break Auxiliary
Contact, For 30A 60A and 100A, Pilot Duty.

Features

- Industrial GradeUnfused Switch
- Break before Main Break Auxiliary Contact
- For 30A 60A and 100A

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current voltage
- Electrical - Dielectric Voltage - Withstands 3,000V Min
- Electrical - Max. Working Voltage - 600V RMS
- Electrical - Operations - Mechanical 10,000 cycles
- Electrical 6,000 cycles
- Environmental - Flammability - Meets UL 94V0 material classification
- Environmental - Moisture Resistance - IP66 suitability
- Environmental - Operating Temperature - Maximum continuous +75°C Minimum continuous -40°C
- Environmental - UV Resistance - All exposed materials are UV stabilized
- Mechanical - Impact Resistance - In accordance with UL 746C
- Mechanical - Mounting - External full adjustable feet
- Mechanical - Product Identification - Identification and ratings are part of the external label and receptacle face
- Mechanical - Terminal Identification - In accordance with UL, CSA

General

Catalog Number	HBLAC2
EU RoHS Indicator	No
Item Type	Switched Enclosure Auxillary Contact
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Non-Fused;Fused
Style	Auxiliary Contacts
Type	Accessories
UPC	783585955131



Dimensions

Weight	1 lb
--------	------

Electrical Ratings

Dielectric Strength	Withstands 3,000V minimum
---------------------	---------------------------

Certifications And Compliance

Industry Standard(s)	• Certified to CSA Standard • Listed to UL Standard • Type 3R and 12K Enclosure Rating
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	15
Pallet Quantity	4750

Product Assets

[Brochures - Circuit-Lock® Motor Disconnects](#)
[Catalog Page - WDK F-3 Catalog Page](#)
[Catalog Page - WDK F-11 Catalog Page](#)
[Catalog Page - WDK B-41 Catalog Page](#)
[Catalog Page - WDK F-7 Catalog Page](#)
[Catalog Page - WDK F-5 Catalog Page](#)
[Catalog Page - WDK B-39 Catalog Page](#)
[Catalog Page - WDK G-23 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_PD1789_INSTALLINST](#)
[Literature - Education Application Guide](#)
[Literature - Food Processing Guide](#)
[Literature - Circuit-Lock® Motor Disconnects](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - Disconnect Switches for Use with Variable Frequency Drives](#)
[Literature - Safety Product Guide](#)

[Literature - Circuit-Lock® Disconnects with LED Indicators](#)
[Literature - Circuit-Lock® Rounded Sloped Top Motor Disconnects](#)
[Literature - Circuit-Lock® 30A Disconnects with LED Indicators](#)
[Literature - Healthcare Application Guide](#)

[Literature - Circuit-Lock® Motor Disconnects with Jog Switch](#)
[Specifications - Wiring HBLAC2 Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Circuit-Lock® Rounded Sloped Top Motor Disconnects](#)
[Video - InSight Motor Disconnects](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK-HBLAC2-SPEC-EN | REV 7/2025