



Straight Blade Devices, SNAPConnect Tester, Circuit Tester for SNAPConnect receptacle terminals, GFCI and standard receptacles

By Hubbell Wiring Device-Kellems
Catalog # [SNAPCTG](#)



Straight Blade Devices, SNAPConnect Tester, Circuit Tester for SNAPConnect receptacle terminals, GFCI and standard receptacles

Features

- 3-in-1 Design. Tests proper wiring of SNAPConnect receptacles, Tests proper wiring of standard receptacles, tests GFCI receptacles

General

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Material	Nylon
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Type	Circuit Tester
UPC	78358555751

Dimensions

Display Size	Standard Sized Product
Height	1.44 in
Length	4.76 in
Weight	0.25 lb

Electrical Ratings

Connectivity	Connectorized
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Conductors	3-Wire Grounding
Number Of Wires	3-Wire

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA, C22.2, No. 42 File 285• Fed. Spec. W-C-596• NEMA® WD-6 Compliant• UL Listed to UL498 File No. E2186
----------------------	--

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Wiring Y-13 Catalog page](#)
[Catalog Page - Wiring A-17 Catalog page](#)
[Catalog Page - Wiring X-13 Catalog page](#)
[Catalog Page - Wiring M7 Catalog page](#)
[Catalog Page - Wiring_Catalog_CC3_CatPage](#)
[Catalogs - Wiring Full Catalog](#)
[Engineering Drawing - SNAPCTG AutoCAD Drawing](#)
[Installation Manuals - WIRING_SNAPCTG_INSTALLINST](#)
[Literature - WLBD026_Duct Products Brochure_WEB](#)
[Sales Drawings - WDK_SNAPCTG_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)
[Video - SNAPConnect Devices](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-SNAPCTG-SPEC-EN | REV 5/2023