



Kellems Wire Management, Pulling Grips, Splicing Grip, 1.00"-1.49", Galvanized, 24" Long

By Hubbell Wiring Device-Kellems
Catalog # [01304015](#)

Kellems® Cable Splicing Grip, 1"-1.49", Galvanized, 24" Long.



Features

- Double weave construction
- Suitable for splicing

Application

Cable and Wire Splicing

General

Approx Breaking Strength	10,000 lbs
Color	<ul style="list-style-type: none">• Metallic• Métallique
Environmental Conditions	No Limitations
Material	Steel, Galvanized
Material - Mounting Hardware	On Cable Ends
Performance	<ul style="list-style-type: none">• Mechanical - Approximate Breaking Strength - 10,000 (44,480) Lbs. (N)• Mechanical - Cable Diameter Range - 1.00"-1.49" (2.54-3.78)• Mechanical - Working Load - (program formula 5% of Approximate Breaking Strength)
Series	Splicing Grips
Style	Closed Mesh, Double Weave
Type	<ul style="list-style-type: none">• Tube• Tube
UPC	783585326993

Dimensions

Display Size 24" (60.96) Length

Conductor Related

Cable Diameter Range 1.00 in-1.49 in
Cable Size 1.00"-1.49" (2.54-3.78)
Number Of Conductors 1 Jacketed Cable

Certifications and Compliance

Industry Standard(s) CSA Certified

Product Assets

- [Catalog Page - WDK W-15 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Literature - WIRING_WLFVM034](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Literature - Wiring_WLFVM032](#)
- [Literature - Wiring_WLBVM044](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK_01304015_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Kellems Wire Management Solutions](#)
- [Video - Kellems Wire Management Solutions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-01304015-SPEC-EN | REV 1/2024