

Kellems Wire Management, Pulling Grips, Overhead Rotating Eye, .50-.74"

By Hubbell Wiring Device-Kellems
Catalog # 03302018

Kellems Wire Management, Pulling Grips, Overhead Rotating Eye, .50-.74"

Features

- Designed for pulling aluminum or copper bare conductor, ground wirres, messenger strands, wire rope and insulated cables

Application

Overhead Pulling

Performance

- Mechanical - Approximate Breaking Strength - 10,000 (44,480) Lbs. (N)
- Mechanical - Cable Diameter Range - .50"-.74" (1.27-1.88)
- Mechanical - Working Load - 2000 (8896) Lbs. (N)

General

Approx Breaking Strength	10,000 lbs
Catalog Number	03302018
Color	Metallic
Color Code	Brown
Construction	Woven
EU RoHS Indicator	Yes
Load Capacity	2000
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
Series	Overhead Multiple Strength
Specifications	• Eye - Steel • Shoulders - Aluminum • Strand - Galvanized Steel • Tag - Mylar
Style	Closed Mesh, Triple, Double, Single Weave



Type	Rotating Eye
UPC	783585314495
Conductor Related	
Cable Diameter Range	0.50 in-0.74 in
Cable Size	.50"-.74" (1.27-1.88)
Cable Specification	UL Listed Circuit Wire

Certifications And Compliance

Industry Standard(s)	CSA Certified
----------------------	---------------

Logistics

Carton Quantity	2
Pallet Quantity	400

Product Assets

- Catalog Page - [WDK W-8 Catalog Page](#)
- Catalogs - [WDK Catalog Full 2024](#)
- Installation Manuals - [WIRING_30920061_INSTALLINST](#)
- Literature - [Wire Management Solutions Brochure](#)
- Literature - [FOOD & BEVERAGE SOLUTIONS](#)
- Literature - [PULP & PAPER SOLUTIONS](#)
- Literature - [Pulp & Paper Solutions](#)
- Literature - [FOOD & BEVERAGE SOLUTIONS](#)
- Sales Drawings - [WDK_03302018_DRAWING_PDF](#)
- Specifications - [03302018 Specification Sheet](#)
- Specifications - [Wiring 03302018 Specification Sheet](#)
- Specifications - [3302018 Specification Sheet French](#)
- Warranty - [Industrial & Commercial Products](#)
- Video - [Kellems Wire Management Solutions](#)
- Video - [Kellems Wire Management Solutions](#)