



Kellems Wire Management, Liquidtight System, 45 Degree, 1 1/4", Non-Insulated with Mesh

By Hubbell Wiring Device-Kellems
Catalog # [074093445](#)

Kellems® Liquidtight System, 45°, 1 1/4" Non-Insulated with Mesh.

Features

- Helps prevent conduit pull-out and damage at fitting
- Reduces equipment downtime

General

Material	Steel Fitting, Stainless Steel Mesh
Performance	<ul style="list-style-type: none">• Environmental - Flammability - UL 94-HB and UL 94-V2• Environmental - Hazardous Location - Suitable for use in hazardous locations per Class I, Div. 2, Class II, Div. 1 & 2, Class III, Div. 1 & 2• Environmental - Operating Temperature - -30°F to +225°F (-34°C to +107°C)
Series	Liquidtight Conduit
Style	For Metal & Non-Metallic PolyTuff I
Type	<ul style="list-style-type: none">• 45 Degree With Male Fitting• 45 Degree With Male Fitting
UPC	783585331843



Dimensions

Conduit Trade Size 1 1/4 in

Certifications and Compliance

Industry Standard(s) UL Listed
Standards - RoHS Compliance CM
Status

Logistics

Carton Quantity 2

Product Assets

[Catalog Page - WDK W-67 Catalog Page](#)
[Catalog Page - WDK W-59 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Engineering Drawing - 074093445 AutoCAD Drawing](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Wire Management Solutions Brochure](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_074093445_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Kellems Wire Management Solutions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-074093445-SPEC-EN | REV 1/2024