




Straight Blade Devices, Decorator Duplex Receptacle, Hospital Grade, Hubbell-Pro, LED Indicator, 15A 125V, 2- Pole3-Wire Grounding, 5-15R, White

By Hubbell Wiring Device-Kellems
Catalog # [2172WL](#)



Straight Blade Devices, Decorator Duplex Receptacle, Hospital Grade, Hubbell-Pro, LED Indicator, 15A 125V, 2- Pole3-Wire Grounding, 5-15R, White.

Features

- Green LED Power Indicators to identify emergency circuits
- Triple wipe contacts
- High impact resistant decorator face
- Steel mounting strap

Application

Hubbell-Pro Heavy Duty Hospital Grade

General

Color	<ul style="list-style-type: none"> • White • Blanc
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Indicator(s) Type	Green LED
Item Type	Style Line Decorator Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94V-2 • Environmental - Operating Temperature - Maximum continuous 75°C, minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal

Dimensions

Dimensions	3.28 in x 1.57 in x 1.15 in
Display Size	Standard Sized Product
Height	1.15 in
Length	3.28 in
Weight	0.2 lb
Width	1.57 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA, C22.2, No. 42 File 285 • Fed. Spec. W-C-596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
----------------------	---

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK L-9 Catalog Page](#)
[Catalog Page - WDK A-26 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)

- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

[Engineering Drawing - 2172WL AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2504_INSTALLINST](#)
[Literature - Duct Products Guide](#)
[Literature - Hubbell-Pro Hospital Grade Receptacles](#)
[Sales Drawings - WDK_2172L_DRAWINGS_PDF](#)
[Warranty - Industrial & Commercial Products](#)

Series Hubbell-Pro
Style Style Line decorator
Type • Duplex Receptacle
 • Duplex Receptacle

UPC 783585196244



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-2172WL-SPEC-EN | REV 1/2024