

Straight Blade Devices, Tamper
Resistant Duplex Receptacle,
Hubbell-Pro, Hospital Grade, LED
Indicator, 2-Pole 3-Wire Grounding,
15A 125V, 5-15R

By Hubbell Wiring Device-Kellems
Catalog # 8200BKLTRA

Straight Blade Devices, Tamper Resistant Duplex Receptacle,
Hubbell-Pro, Hospital Grade, LED Indicator, 2-Pole 3-Wire
Grounding, 15A 125V, 5-15R, Black

Features

- Tamper-resistant shutter complies with national electrical code requirements
- Green LED Power Indicators to identify emergency circuits
- Triple wipe contacts
- High impact resistant face with circuit I.D. marking area
- Steel mounting strap

Application

Hubbell-Pro Heavy Duty Hospital Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	8200BKLTRA
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	0.5
Indicator(s) Type	Green LED
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Hubbell-Pro



Specifications

- Automatic Self-grounding Staple - Stainless steel
- Base - PBT
- Clamping Plate - Plated steel
- Face - Nylon
- Ground Contacts - Brass
- Mounting Screws - Zinc plated steel
- Mounting Strap - Galvanized steel
- Power Contacts - Brass

Style
Type
UPC

Smooth Face
Receptacle
783585542089

Dimensions

Dimensions	3.28 in x 1.57 in x 1.15 in
Height	1.15 in
Length	3.28 in
Weight	0.2 lb
Width	1.57 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA, C22.2, No. 42 File 285• Fed. Spec. W-C-596• NEMA® WD-6 Compliant• UL Listed to UL498 File No. E2186
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK A-27 Catalog Page](#)
- [Catalog Page - WDK L-8 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Tamper-Resistant Receptacles for Healthcare](#)
- [Literature - Duct Products Guide](#)
- [Literature - Hubbell-Pro Hospital Grade Receptacles](#)
- [Literature - Hubbell-PRO Hospital Grade TR Receptacles](#)
- [Specifications - 8200BKLTRA](#)
- [Specifications - 8200BKLTRA Specification Sheet French](#)
- [Specifications - 8200BKLTRA Specification Sheet English](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Tamper-Resistant Receptacles](#)
- [Video - Tamper-Resistant Receptacles](#)



A Hubbell brand