

Straight Blade Devices, Tamper  
Resistant, Duplex Receptacle,  
Hospital Grade, Hubbell-Pro, LED  
Indicator, 20A 125V, 2-Pole 3-Wire  
Grounding, 5-20R

By Hubbell Wiring Device-Kellems  
Catalog # 8300BKLTRA

Straight Blade Devices, Tamper Resistant, Duplex Receptacle,  
Hospital Grade, Hubbell-Pro, LED Indicator, 20A 125V, 2-Pole 3-  
Wire Grounding, 5-20R, Black

Features

- Tamper-resistant shutter complies with national electrical code requirements
- Green LED Power Indicators to identify emergency circuits
- Triple wipe contacts
- High impact resistant face with circuit I.D. marking area
- Steel mounting strap

Application

Hubbell-Pro Heavy Duty Hospital Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12-#10 AWG stranded or solid copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	8300BKLTRA
Horsepower - Maximum	1
Indicator(s) Type	Green LED
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Hubbell-Pro
Specifications	<ul style="list-style-type: none"><li>• Face: Nylon</li></ul>



- Base: PBT
- Power Contacts: Brass
- Ground Contacts: Brass
- Clamping Plate: Plated steel:Mounting Strap: Galvanized steel
- Automatic Self-grounding Staple: Stainless steel
- Mounting Screws: Zinc plated steel

Style	Smooth Face
Type	Receptacle
UPC	783585542256

Dimensions

Dimensions	3.28 in x 1.57 in x 1.15 in
Height	1.15 in
Length	3.28 in
Weight	0.2 lb
Width	1.57 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA, C22.2, No. 42 File 285</li><li>• Fed. Spec. W-C-596</li><li>• NEMA® WD-6 Compliant</li><li>• UL Listed to UL498 File No. E2186</li></ul>	<a href="#">Catalog Page - WDK A-27 Catalog Page</a> <a href="#">Catalog Page - WDK L-8 Catalog Page</a> <a href="#">Catalogs - WDK Catalog Full 2024</a> <a href="#">Literature - Tamper-Resistant Receptacles for Healthcare</a> <a href="#">Literature - Duct Products Guide</a> <a href="#">Literature - Hubbell-Pro Hospital Grade Receptacles</a> <a href="#">Literature - Hubbell-PRO Hospital Grade TR Receptacles</a> <a href="#">Specifications - 8300BKLTRA Specification Sheet French</a> <a href="#">Specifications - 8300BKLTRA Specification Sheet</a> <a href="#">Specifications - Wiring 8300BKLTRA Specification Sheet</a> <a href="#">Warranty - Industrial &amp; Commercial Products</a> <a href="#">Video - Tamper-Resistant Receptacles</a> <a href="#">Video - Tamper-Resistant Receptacles</a>
Nema Rating	5-20R	
<b>Logistics</b>		
Carton Quantity	10	
<b>Product Assets</b>		

