



Straight Blade Devices, Receptacles, Tamper-Resistant Duplex, Commercial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5 -15R, Black, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [CRI5BLKTR](#)



Straight Blade Tamper-Resistant Duplex Receptacle,
Commercial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5 -15R.

Features

- Tamper-resistant shutter complies with national electrical code requirements
- Smooth face
- Triple wipe contacts

Application

Commercial Specification Grade

General

Color	<ul style="list-style-type: none"> • Black • Noir
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94 V-2 • Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal Accommodation - #14-#10 AWG stranded or solid

Dimensions

Dimensions	1.32 in x 0.83 in x 3.28 in
Display Size	Standard Sized Product
Height	3.28 in
Length	1.32 in
Weight	0.15 lb
Width	0.83 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA, C22.2, No. 42 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
Nema Rating	5-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK AA-43 Catalog Page](#)
[Catalog Page - WDK A-28 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Engineering Drawing - M10512_ACAD](#)

	copper wire only
	<ul style="list-style-type: none">Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA
Series	Commercial Specification Grade
Style	Smooth Face
Type	<ul style="list-style-type: none">Tamper-ResistantTamper-Resistant
UPC	783585144207

[Literature - Tamper-Resistant Receptacles for Daycare](#)
[Literature - Tamper-Resistant Receptacles for Assisted Living](#)
[Literature - Tamper-Resistant Receptacles for Education](#)
[Literature - Tamper-Resistant Receptacles for Hospitality](#)
[Literature - Tamper-Resistant Specification Grade Receptacles](#)
[Literature - Tamper-Resistant Receptacles](#)
[Literature - Hubbell Marine Full Line Catalog](#)
[Sales Drawings - M10512](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Marine Electrical Products](#)
[Video - Tamper-Resistant Receptacles](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-CR15BLKTR-SPEC-EN | REV 1/2024