

Straight Blade Devices,
Receptacles, Duplex, Hubbell-Pro
Heavy Duty, 2-Pole 3-Wire
Grounding, 20A 125V, 5-20R, Gray,
Single Pack, Isolated Ground.

By Hubbell Wiring Device-Kellems
Catalog # [CR5352IGGY](#)



Straight Blade Duplex Receptacle, Hubbell-PRO Heavy Duty, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Isolated Ground

Features

- Triangle marking on face indicates isolated ground
- Slender/compact design
- Finder Groove Face

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	CR5352IGGY
EU RoHS Indicator	Yes
Horsepower - Maximum	1
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Hubbell-PRO
Specifications	<ul style="list-style-type: none">• Automatic Self-grounding Clip - Stainless steel• Base - PBT• Clamp - Nickel plated steel• Face - Nylon• Ground Contacts - .031" (.8) Brass• Mounting Screws - Stainless Steel

Style
UPC

- Mounting Strap - .040" (1) Galvanized steel
 - Mounting Strap - Galvanized steel
 - Terminal Screws - Brass
- Finder Groove Face
783585387192

Dimensions

Dimensions	3.28 in x 1.33 in x 1.05 in
Display Size	Standard Sized Product
Height	1.05 in
Length	3.28 in
Weight	0.22 lb
Width	1.33 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA, C22.2, No. 42 File 285• Fed. Spec. WC596• NEMA® WD-6 Compliant
----------------------	--

	<ul style="list-style-type: none">UL Listed to UL498 File No. E2186
Nema Rating	5-20R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- Catalog Page - WDK A-28 Catalog Page
- Catalog Page - WDK I-4 Catalog Page
- Catalog Page - WDK M-17 Catalog Page
- Catalogs - WDK Catalog Full 2024
- Installation Manuals - WIRING_PD2615_INSTALLINST
- Sales Drawings - WDK_CR5352IG_DRAWING_PDF
- Specifications - Wiring CR5352IGGY Specification Sheet
- Specifications - CR5352IGGY Specification Sheet French
- Specifications - CR5352IGGY Specification Sheet
- Warranty - Industrial & Commercial Products

