

Spec Grade, Illuminated Decorator
Switches, General Purpose AC, Single Pole,
20A 120/277V AC, Back and Side Wired,
Pre-Wired with 8" #12 THHN

By Hubbell Wiring Device-Kellems
Catalog # [DS120ILBK](#)

Switches and Lighting Controls, Spec Grade, Illuminated
Decorator Switches, General Purpose AC, Single Pole, 20A
120/277V AC, Back and Side Wired, Pre-Wired with 8" #12 THHN,
Black

Features

- Thread cleaning captive mounting screw
- Steel, zinc plated bridge is corrosion resistant
- Automatic self-grounding staple

Performance

Electrical - Dielectric Voltage - Withstands 1500V AC minimum
for 1 minute, Electrical - Max. Continuous Current - 20A, Electrical
- Max. Working Voltage - 277V AC, Electrical - Overload -
Minimum 4.8 times rated current for 100 cycles, Electrical -
Temperature Rise - 30°C maximum at rated current,
Environmental - Flammability - UL 94V-2, Environmental -
Operating Temperature - Max. continuous: 75°C, Min. continuous:
-40°C without impact, Mechanical - Terminal Accommodations -
#14 AWG min. - #10 AWG max. solid and stranded copper wire
only

Specifications

EU RoHS Indicator	No
Industry Standard(s)	UL Listed

Conductor

Wire Size	#14 AWG to #10 AWG
Number Of Poles	Single Pole

Current

Amperage Rating	20 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Current Rating	20 A
Voltage Rating	120-277 VAC
Temperature Rise - Max.	30°C maximum at rated current
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A

Dimensions

Length	4.28 in
--------	---------



Weight	0.2 lb.
Height	1.54 in
Width	1.43 in
Dimensions	4.28 in x 1.43 in x 1.54 in

General

Color	Black
Style	Single Pole
Series	Illuminated
Specifications	• Contacts - Silver Alloy • Contacts - Silver Alloy • Ground Screw - Brass (Green) • Mounting Bridge - Nickel Plated Steel with Auto Ground Staple • Rocker Material - Thermoplastic • Terminal Screws - Brass
UPC	783585187884
Type	Rocker/Decorator
Item Type	Single Pole Style Line Illuminated Decorator Switch Thermoplastic
Material	

Logistics

Carton Quantity	10
-----------------	----

Operational

Indicator	Light On with Load Off
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Indicator(s) Type	Blue LED

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)