

Decorator Series Specification Grade,
Rocker Switches, General Purpose AC,
Illuminated Single Pole, 20A 120/277V AC,
Back and Side Wired

By Hubbell Wiring Device-Kellems
Catalog # [DS120ILW](#)

Switches and Lighting Controls, Decorator Series Specification Grade, Rocker Switches, General Purpose AC, Illuminated Single Pole, 20A 120/277V AC, Back and Side Wired, White

Features

- Thread cleaning captive mounting screw
- Steel, zinc plated bridge is corrosion resistant
- Automatic self-grounding staple

Performance

Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute, Electrical - Max. Continuous Current - 20A, Electrical - Max. Working Voltage - 277V AC, Electrical - Overload - Minimum 4.8 times rated current for 100 cycles, Electrical - Temperature Rise - 30°C maximum at rated current, Environmental - Flammability - UL 94V-2, Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact, Mechanical - Terminal Accommodations - #14 AWG min. - #10 AWG max. solid and stranded copper wire only

Specifications

EU RoHS Indicator	No
Industry Standard(s)	UL Listed

Conductor

Wire Size	#14 AWG to #10 AWG
Number Of Poles	Single Pole

Current

Amperage Rating	20 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Current Rating	20 A
Voltage Rating	120-277 VAC
Temperature Rise - Max.	30°C maximum at rated current
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A

Dimensions

Length	4.28 in
Weight	0.2 lb.



Height	1.54 in
Width	1.43 in
Dimensions	4.28 in x 1.43 in x 1.54 in

General

Color	White
Style	Single Pole
Series	Illuminated
Specifications	• Contacts - Silver Alloy • Contacts - Silver Alloy • Ground Screw - Brass (Green) • Mounting Bridge - Nickel Plated Steel with Auto Ground Staple • Rocker Material - Thermoplastic • Terminal Screws - Brass
UPC	783585154572
Type	Rocker/Decorator
Item Type	Single Pole Style Line Illuminated Decorator Switch
Material	Thermoplastic

Logistics

Pallet Quantity	4050
Carton Quantity	10

Operational

Indicator	Light On with Load Off
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Indicator(s) Type	Blue LED

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)