



# Switches and Lighting Control, Decorator Switch, Specification Grade, Four Way, 20A 120/277V AC, Back and Side Wired, Gray

By Hubbell Wiring Device-Kellems  
Catalog # [DS420GY](#)



Decorator Switch, Specification Grade, Four Way, 20A  
120/277V AC, Back and Side Wired.

## Features

- Thread cleaning captive mounting screw
- Steel, zinc plated bridge is corrosion resistant
- Automatic self-grounding staple

## General

Action	DPDT
Color	<ul style="list-style-type: none"> <li>• Gray</li> <li>• Gris</li> </ul>
Item Type	Four Way Style Line Decorator Switch
Material	Thermoplastic
Number Of Poles	Double Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute</li> <li>• Electrical - Max. Continuous Current - 20A</li> <li>• Electrical - Max. Working Voltage - 277V AC</li> <li>• Electrical - Overload - Minimum 4.8 times rated current for 100 cycles</li> <li>• Electrical - Temperature Rise - 30°C maximum at rated current</li> <li>• Environmental - Flammability - UL 94V-2</li> <li>• Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact</li> <li>• Mechanical - Terminal Accommodations - #14 AWG min. - #10 AWG max. solid and stranded copper wire only</li> </ul>
Series	General Purpose

## Dimensions

Dimensions	4.28 in x 1.73 in x 1.67 in
Height	1.67 in
Length	4.28 in
Weight	0.2 lb
Width	1.73 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC

## Conductor Related

Wire Size	#14 AWG to #10 AWG
-----------	--------------------

## Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - WDK D-12 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2023](#)  
[Installation Manuals - WIRING\\_PD2444\\_INSTALLINST](#)  
[Sales Drawings - WDK\\_DS420\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)

Style

Four Way

Type

- Rocker/Decorator

- Rocker/Decorator

UPC

783585154480



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-DS420GY-SPEC-EN | REV 1/2024