

Extra Heavy Duty Industrial
Tamper-Resistant/Weather
Resistant AUTOGUARD® Self-Test
GFCI Receptacle, 20A, Ivory

By Hubbell Wiring Device-Kellems
Catalog # [GFSG5362I](#)



20A, 125V Industrial Grade, Tamper-Resistant, Weather-Resistant, Ground Fault Receptacle.

Features

- Heavy duty robust construction, high impact resistant polyester housing
- Corrosion Resistant: nickel-plated face contacts, mounting strap, line/load terminals and terminal clamps, stainless steel screws
- Patented auto monitor, power denial technology

General

Catalog Number	GFSG5362I
Item Type	Style Line GFCI Receptacle
Material	PC/PBT
Series	Extra Heavy Duty
Size	4.06 in x 1.75 in x 1.48 in
Specifications	<ul style="list-style-type: none">• Base - Nylon• Face - PC/PBT• Ground Contacts - Nickel Plated Brass• Mounting Screws - Stainless Steel• Mounting Strap -Nickel Plated Brass
UPC	783585745961

Dimensions

Dimensions	1.48 in x 1.75 in x 4.06 in
Height	4.06 in
Length	1.48 in
Width	1.75 in

Electrical Ratings

Current / Amperage Rating	20 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	2500 W

Conductor Related

Wire Size	#14 - #10 AWG
-----------	---------------

Certifications And Compliance

Industry Standard(s)	UL 943 and Meets All NEC® Requirements
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK K-3 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - PD2987](#)
- [Literature - Hospital Grade GFCI Receptacles CA](#)
- [Literature - Extra Heavy Duty Industrial GFCI Receptacles](#)
- [Literature - FREQUENTLY ASKED QUESTIONS Industrial and hospital grade GFCI receptacles](#)
- [Sales Drawings - M14626](#)
- [Specifications - GFSG5362I](#)
- [Specifications - GFSG5362I Specification Sheet English](#)
- [Specifications - GFSG5362I](#)
- [Warranty - Industrial & Commercial Products](#)