

GFCI Circuit Breaker Sensing  
Module with Auto Reset, 4-6mA  
Trip Level, 120V AC, Black

By Hubbell Wiring Device-Kellems  
Catalog # [GFSMST120A](#)



Power Protection Product, GFCI Circuit Breaker Sensing  
Modules, Industrial, Auto Set, 120V AC, GFCI Circuit Breakers, 4-  
6 mA Trip Level, Black

Features

- Must be used with GSMCB GFCI Sensing Module Circuit Breaker
- Functions interdependently with a magnetic branch circuit breaker
- Monitors the electrical circuit by use of an external differential current transformer
- No direct load is present at the module
- Self-test functionality per UL 943

Application

Heavy Duty Industrial Commercial

General

Auxiliary Contacts	None
Catalog Number	GFSMST120A
EU RoHS Indicator	No
Enclosure Type	Yes
Environmental Conditions	NEMA 4X
Frame	Standard
Item Type	Auto Set Sensing Module
Material	Composite
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Series	Extra Heavy Duty
Type	Auto Reset
UPC	783585703237

Dimensions

Dimensions	4.6 in x 2.8 in x 3.3 in
Height	3.3 in
Length	4.6 in
Width	2.8 in

Electrical Ratings

Connectivity	Terminal Screws
Frequency Rating	60 Hz
Interrupt Rating	10,000 A
Load Rating	80% of Full Rating Continuous A
Trip Type	.025 Seconds
Voltage Rating	120 VAC
Voltage Rating Description	120 VAC

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Product Assets

[Catalog Page - WDK K-12 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Safety Product Guide](#)  
[Literature - PULP & PAPER SOLUTIONS](#)  
[Literature - Pulp & Paper Solutions](#)  
[Sales Drawings - M-14592](#)  
[Specifications - GFSMST120A Specification Sheet French](#)  
[Specifications - WIRING\\_GFSMST120A\\_spec](#)  
[Specifications - GFSMST120A Specification Sheet](#)  
[Warranty - Industrial & Commercial Products](#)