



Kellems Wire Management, Liquidtight System, 45 Degree Male Liquid Tight Connector, 1 1/4", Steel, Non-Insulated

By Hubbell Wiring Device-Kellems
Catalog # [H1254](#)



Kellems Wire Management, Liquidtight System, 45 Degree Male Liquid Tight Connector, 1 1/4", Steel, Non-Insulated.

Features

- Hexagonal nut compresses gland-ring onto conduit
- Nylon gasket provides liquidtight seal at hub
- Non-integral steel ferrule seals conduit

Application

For use with Liquidtight Metal conduit and PolyTuff I Non-Metallic conduit

General

Material	Iron, Zinc Plated
Performance	<ul style="list-style-type: none">• Environmental - Operating Temperature - -60°F to +1000°F (-51°C to +538°C)• Environmental - Hazardous Locations - NEC Reference -Class I, Div. 2 - 501-10(A)(3)B, Class II, Div. 1 - 502-10(A)(2), Class II, Div. 2 - 502-10(A)(3), Class III, Div. 1 - 503-10(A)(2), Class III, Div. 2 - 503-10(B)
Style	45°
Type	<ul style="list-style-type: none">• Metallic Liquidtight Fittings• Metallic Liquidtight Fittings
UPC	783585034454

Dimensions

Dimension - Thread Size	1-1/4"-11-1/2 NPT
Dimension - Width mm	2.187 in
Trade Size	1 1/4

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified• UL 514B
----------------------	---

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog Page - WDK W-91 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Engineering Drawing - H1254 AutoCAD Drawing](#)
[Literature - Wire Management Solutions Brochure](#)
[Sales Drawings - WDK_H1254_DRAWINGS_PDF](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Kellems Wire Management Solutions](#)

Related Products

[074093445 - Kellems Wire Management, Liquidtight System, 45 Degree, 1 1/4", Non-Insulated with Mesh](#)
[G1125 - Kellems Wire Management, Liquidtight System, Non-Metallic PolyTuff® I Conduit, Gray, 1-1/4", 100 feet](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-H1254-SPEC-EN | REV 1/2024