

Extra Heavy Duty Industrial Grade,
Locking Toggle Switches, General
Purpose AC, Single Pole, 15A
120/277V AC, Back and Side Wired
Key Guide

By Hubbell Wiring Device-Kellems
Catalog # [HBL1201LI](#)

Switches and Lighting Controls,Extra Heavy Duty Industrial
Grade, Locking Toggle Switches, General Purpose AC, Single
Pole, 15A 120/277V AC, Back and Side Wired, Ivory Key Guide

Features

- Large brass binding head screws with deep slots
- Lock circuits On or Off
- Strip gauge for accurate wiring

Application

Back and Side Wired

Performance

- Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute
- Electrical - Max. Continuous Current - 15A
- Electrical - Max. Working Voltage - 277V AC
- Electrical - Overload - Minimum 4.8 times rated current for 100 cycles
- Electrical - Temperature Rise - 30°C maximum at rated current
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact
- Mechanical - Terminal Accommodations - #14 AWG min. - #10 AWG max. solid and stranded copper wire only

General

Catalog Number	HBL1201LI
EU RoHS Indicator	No
Number Of Poles	Single Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none">• Base Material - Thermoset, Blue• Contacts - Silver Alloy• Ground Screw - Brass (Green)• Key Guide - Metallic, Ivory• Terminal Screws - Brass



Style	• Top Material - Thermoset
Type	Single Pole
UPC	Locking 783585188447
Dimensions	
Dimensions	4.06 in x 1.31 in x 1.13 in
Height	1.13 in
Length	4.06 in
Width	1.31 in
Electrical Ratings	
Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC
Voltage Rating Description	120-277 VAC

Conductor Related

Wire Size	#14 AWG to #10 AWG
-----------	--------------------

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK D-3 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBL1201LI AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1242_INSTALLINST](#)

[Sales Drawings - WDK_HBL1201L_DRAWING_PDF](#)
[Specifications - HBL1201LI Specification Sheet French](#)
[Specifications - HBL1201LI Specification Sheet](#)

[Specifications - Wiring HBL1201LI Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK_CA-HBL1201LI-SPEC-EN | REV 4/2025