

HUBBELL
Wiring Device-Kellems

**Switches and Lighting Control,
Fluorescent High Bay Photocell
Sensor, PIR, 1 Relay, Universal, Low
Temp, 120-347V AC, Water Tight**

By Hubbell Wiring Device-Kellems
Catalog # [HMHB21UPCW](#)

Switches and Lighting Control, Fluorescent High Bay Photocell
Sensor, PIR, 1 Relay, Universal, Low Temp, 120-347V AC, Water
Tight



Features

- Digital passive infrared sensor. Low profile design, no minimum load
- Two (2) Built-in photocell for daylight harvesting
- 120-347V AC, 1 relay
- Supports mounting heights up to 45 ft for high bay configurations and between 8-16 ft for low bay configurations

General

Color	White
EU RoHS Indicator	No
Operating Temperature	-40°F to 149°F (-40°C to 65°C)
Performance	Electrical - Lighting Load Capacity - 120V AC 0-800 watts ballast, tungsten LED driver. 277V AC 0-1200 watts ballast, LED driver. 347V AC 0-1500 watts ballast, LED driver Environment - - IP65 Suitability Environment - Operating temperature - -40°F to 149°F (-40°C to 65°C) Environment - Relative humidity - 0% to 95% Motor load - - 1/4HP @ 120V AC, 1/6 HP @ 347V Timer time-outs - Primary - 8-second test mode 4, 8, 16 and 30 minutes. Timer time-outs - Secondary - Disabled, 30, 60 and 90 minutes. Available on dual relay versions only. User Interface - 12-pin DIP switch
Photocell	Yes
Series	High/Low Bay PIR
Style	Sensors
Type	Sensors
UPC	783585256047

Electrical Ratings

Voltage Rating	120-347 VAC
Voltage Rating Description	120/347V AC

Certifications And Compliance

Industry Standard(s)	CEC Title 24 Certified cULus Listed Meets ASHRAE 90.1
Nema Rating	NEMA 3R

Logistics

Carton Quantity 12

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_PD2532_INSTALLINST](#)
[Literature - Load Control Application Guide](#)
[Literature - Food Processing Guide](#)
[Literature - Healthcare Application Guide](#)
[Sales Drawings - WDK_HMHB21UPCW_DRAWING_PDF](#)
[Warranty - HMOSS Occupancy Motion Sensors](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK-HMHB21UPCW-SPEC-EN | REV 6/2024