



Locking Devices, Twist-Lock®, Watertight Safety Shroud, Receptacle, 20A 125V, 2-Pole 3- Wire Grounding, L5-20R, Screw Terminal, Gray



By Hubbell Wiring Device-Kellems
Catalog # [HBL2310SW](#)

Twist-Lock® Watertight Safety-Shroud® Receptacle, 20A 125V,
2-Pole, 3-Wire Grounding, NEMA L5-20R, PBT Housing and
Flange.

Features

- UL type 4X environmental seal while in use and when closed
- High impact, thermoplastic housing for heavy-duty industrial environments
- Alignment arrows with lock and unlock symbols provide a visual indication that devices are properly connected
- Catalog number and color coded voltage rating are visible even when in use
- Catalogue number and color coded voltage rating are visible even when in use

Application

Heavy Duty Industrial Shrouded Watertight

General

Color	<ul style="list-style-type: none"> • Gray • Gris
Environmental Conditions	Watertight
Horsepower - Maximum	1
Item Type	20A Watertight Safety-Shroud® Receptacle
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17 • Environmental - Moisture Resistance - IP20 Suitability

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 VAC

Conductor Related

Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

Certifications and Compliance

Industry Standard(s)	UL Listed, CSA Certified To Type 4, 4X And Type 12
----------------------	--

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalog Page - WDK H-13 Catalog Page](#)
- [Catalog Page - WDK C-3 Catalog Page](#)
- [Catalog Page - WDK B-41 Catalog Page](#)
- [Catalog Page - WDK B-21 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - HBL2310SW AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1267_INSTALLINST](#)
- [Literature - Food Processing Guide](#)
- [Literature - Industrial Solutions](#)
- [Literature - Education Application Guide](#)
- [Literature - Safety Product Guide](#)
- [Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)
- [Literature - Entertainment Product Solution Guide](#)
- [Sales Drawings - WDK_HBL2310SW_DRAWINGS_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Insulgrip Twist-Lock and Straight Blade Devices](#)
- [Video - Twist-Lock Devices](#)

Related Products

[AA203055 - Pin and Sleeve Products, Receptacle or Inlet](#)

- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

Angle Adapter, 20 or 30A

HBL2311SW - Locking Devices, Twist-Lock®, Watertight Safety Shroud, Male Plug, 2-Pole 3-Wire Grounding, L5-20P, Screw
 HBLMITL - Heavy Duty Products, Switched Twist-Lock®, Industrial Grade, Accessories, Mechanical Interlock, 30A 600V AC, Single Conductor, Terminal Screws, Gray

BB301W - Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Back Box, For 20A and 30A 1" NPT Hub, Angled, Mounting Screws Included

BB2030N - Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Back Box, For 20A and 30A 3/4" NPT Hub, Angled, MountingScrews Included

Type

- Device
- Device

UPC

783585231006

Dimensions

Dimensions	3.75 in x 3.75 in x 2.69 in
Display Size	Standard Sized Product
Height	2.69 in
Length	3.75 in
Weight	0.55 lb
Width	3.75 in



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
 WDK_CA-HBL2310SW-SPEC-EN | REV 1/2024