



Hospital Grade Surge Suppression Receptacle, 20A 125V, 5-20R, Gray

By Hubbell Wiring Device-Kellems
Catalog # [IG8362WSA](#)

Hospital Grade Surge Suppression Receptacle, 20A 125V, 5-20R, Gray



Features

- High-impact nylon face resists breakage
- Automatic grounding clip attached to bridge
- Power-on indicator light verifies instantly that power is available
- Distinctive surge symbol provides quick visual identification of surge suppression receptacle

Application

Decorator Duplex with Light and Alarm

General

Color	White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED and Audible Alarm
Item Type	Surge Protection Receptacles
Material	Composite
Material - Mounting Hardware	Mounting Screws
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Performance	<ul style="list-style-type: none"> • Electrical - Frequency - 60Hz • Electrical - Protection Modes - Normal and Common Modes • Electrical - Response Time - Approximately 5 ns • Electrical - Transient Suppression - Peak Energy (10 X 100 μs) Peak Current (8 X 20 μs) • Electrical - Voltage - 120V AC + 10% - 15% • Environmental - Flammability - UL 94V-2 • Environmental - Operating Temperature - 32°F to 140°F (0°C to 60°C)
Response Time	5
Series	Hospital Grade
Style	Isolated Ground

Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified to Specification C22.2 No. 42 • Listed to UL Standards 498 Receptacles • UL Listed File E2186
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Wiring M16 Catalog page](#)
[Catalog Page - Wiring N-13 Catalog page](#)
[Catalogs - Wiring Full Catalog](#)
[Engineering Drawing - IG8362WSA AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1152_INSTALLINST](#)
[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs: 4, 6, 8 and 10 inch](#)
[Literature - WLBD026_Duct Products Brochure_WEB](#)
[Literature - Healthcare Application Guide](#)
[Literature - SpikeShield® Power Quality Surge Protective Devices](#)
[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)
[Sales Drawings - WDK_IG8362_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)

Related Products

[SS8 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) Duplex Opening, Standard Size, Stainless Steel](#)
[IG5362WSA - Surge Protective Devices, SPIKESHIELD IG TVSS Duplex Receptacle with Light and Alarm, 20A 125V, 5-20R, White](#)
[P8W - Wallplate, 1-Gang, 1\) Duplex, White](#)
[HBL420S - Surge Protective Devices, 4- PLEX, Surge Suppression Receptacle, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, White](#)

Type
UPC

Duplex
783585060972

5-20R, Blue.
HBL5362WSA - Surge Protective Devices, SPIKESHIELD TVSS
Duplex Receptacle with Light and Alarm, 20A 125V, 5-20R,
White

Dimensions

Display Size Standard



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-IG8362WSA-SPEC-EN | REV 5/2023